


WELL-X-TROL®

Pre-pressurized diaphragm-type well tanks WX-100, 200 and 300 SERIES



In-Line Models

Model		ınk ol.	Max. Accept.		A Height		B Diameter		Factory Pre-charge	Working Pressure	Sh W	nip /t.
No.	Lit	Gal	Factor	mm	in	mm	in	in	PSIG	PSIG ²	kg	lb
WX-101	8	2.0	0.45	321	125/8	203	8	3/4	18	150	2.3	5
WX-102	17	4.4	0.55	381	15	279	11	3/4	18	150	4.0	9
WX-103	33	7.6	0.42	629	221/4	279	11	3/4	28	150	7.0	15
WX-104	39	10.3	1.00	451	173/4	390	15³/ ₈	1	38	150	9.0	20
WX-200	53	14.0	0.81	559	22	390	15³/ ₈	1	38	150	10.0	22

¹ System Connection: Stainless Steel Waterway. ² 150 PSIG is 1034 kPa.

Stand Models

		nk	Max.		-	E		C	Sys.	Factory	Working		nip
Model	V		Accept.		ght			Conn.3		Pre-charge			/t.
No.	Lit.	Gal	Factor	mm	ins.	mm	ins.	ins.	ins.	PSIG	PSIG ²	kg	lbs.
WX-104-S	39	10.3	1.00	489	19¹/₄	390	15³/ ₈	113/16	1	38	150	10.5	23
WX-201	53	14.0	0.81	606	237/8	390	15³/ ₈	113/16	1	38	150	11.4	25
WX-202	76	20.0	0.57	803	315/8	390	15³/ ₈	113/16	1	38	150	15.0	33
WX-202XL	98.4	26.0	0.44	971.5	38 ¹ / ₄	390.5	15³/ ₈	113/16	1	38	150	16.3	36
WX-203	121	32.0	0.35	1143	45	390	15³/ ₈	113/16	1	38	150	20.0	43
WX-205	129	34.0	1.00	752	295/8	559	22	23/16	11/4	38	150	28.0	61
WX-250	167	44.0	0.77	914	36	559	22	23/16	11/4	38	150	31.0	69
WX-251	235	62.0	0.55	1187	463/4	559	22	23/16	11/4	38	150	41.0	92
WX-255	306.6	81.0	0.41	1432	56 ³ / ₈	558.8	22	23/16	11/4	38	150	47.0	103
WX-302	326	86.0	0.54	1200	471/4	660	26	23/16	11/4	38	150	56.0	123
WX-350	450	119.0	0.39	1572	61 ⁷ / ₈	660	26	23/16	11/4	38	150	75.0	166

² 150 PSIG is 1034 kPa.

Max. Operating Conditions

Operating Temperature	200° F (93° C)
Complies with Low Lead Plum	bing Law

Specifications

Description	Standard Construction
Shell	Steel
Diaphragm	Heavy Duty Butyl
Liner	Polypropylene
Coating	Tuf-Kote™ Coating Technology

All dimensions are approximate.



Job Name	Contractor P.O. No.
Location	Sales Representative
	Model No. Ordered
	Pump Cut-In PSI
Engineer	Pump Cut-Out PSI
Contractor	Pump GPM PSI

³ System Connection: Stainless Steel.



WELL-X-TROL®

Pre-pressurized diaphragm-type well tanks


Underground Models



Model		ınk ol.	Max. Accept.	He	ight	Diam	neter	Sys. Conn. ¹	Factory Precharge	Sh W	•
No.	Lit.	Gal	Factor	mm	ins.	mm	ins.	PSIG		kg	lbs.
WX-200-UG	53	14.0	0.81	559	22	390	15³/ ₈	1	38	10.0	22
WX-202-UG	76	20.0	0.57	726	30	390	15³/ ₈	1	38	13.6	30
WX-250-UG	167	44.0	0.77	848	333/8	559	22	11/4	38	27.0	60
WX-251-UG	235	62.0	0.55	1121	441/8	559	22	11/4	38	38.0	83

¹ System Connection: Stainless Steel Coupling. Coating on underground models is an epoxy-based paint. Working Pressure: 150 PSIG (1034 kPa)

Pump Stand Models



			nsions	Total	Max.	Sy	stem Drawo	Shipping	
Model	Height	Width	Length	Volume	Accept.	20/40	30/50	40/60	Wt. (Vol.)
No.	(ins)	(ins)	(ins)	(gals)	Factor	(gals)	(gals)	(gals)	lbs (cu ft)
WX-102-PS	12 1/16	11	15 5/16	4.4	0.55	1.8	1.5	1.3	13 (1.4)
WX-105-PS	11	10 1/2	18 1/4	5.3	0.80	2.1	1.8	1.6	13 (1.5)
WX-110-PS	12 1/8	11	20 9/16	7.4	0.43	2.7	2.3	1.9	15 (2.0)
WX-200-PS	15 3/8	15 3/8	20 7/8	14.0	0.81	5.6	4.8	4.1	29 (4.0)
WX-202-PS	16	15 3/8	27 13/16	20.0	0.57	8.0	6.8	5.9	33.5 (4.9)

Precharge Pressure is 38 PSIG for all models.

Maximum Working Pressure is 150 PSIG and Maximum Working Temperature is 200° F.

Maximum Operating Conditions

Operating Temperature	200° F (93° C)
Working Pressure	
Pump Stand Models	150 PSIG (1034 kPa)
Working Pressure	
UG Models	150 PSIG (1034 kPa)

Complies with Low Lead Plumbing Law

Specifications

Description	Standard Construction			
Shell	Steel			
Diaphragm	Heavy Duty Butyl			
Liner	Polypropylene			
Coating	Pump Stand Models Tuf-Kote™ Coating Technology			


All dimensions are approximate.

Contractor P.O. No.
Sales Representative
Model No. Ordered
Pump Cut-InPSI
Pump Cut-OutPSI
Pump GPMPSI



WELL-X-TROL® PRO Access®

Pre-pressurized diaphragm-type well tanks Stainless steel system connection piped to the stand



Stand Models

Model		nk ol.	Max. Accept.	Hei	\ ght	1	3 neter	Sys. Conn. ¹	Factory Pre-charge	Working Pressure		nip /t.
No.	Lit.	Gal	Factor	mm	ins.	mm	ins.	ins.	PSIG	PSIG ²	kg	lbs.
WX-202P	76	20.0	0.57	803	315/8	390	15³/ ₈	1	38	150	15.0	33
WX-202XLP	98.4	26.0	0.44	971.5	38 ¹ / ₄	390.5	15³/ ₈	1	38	150	16.3	36
WX-203P	121	32.0	0.35	1181	46 ¹ / ₂	390	15³/ ₈	1	38	150	20.0	43
WX-205P	129	34.0	1.00	752	295/8	559	22	11/4	38	150	28.0	61
WX-250P	167	44.0	0.77	914	36	559	22	11/4	38	150	31.0	69
WX-251P	235	62.0	0.55	1187	463/4	559	22	11/4	38	150	41.0	92
WX-255P	306.6	81.0	0.41	1432	56 ³ / ₈	558.8	22	11/4	38	150	38.4	103
WX-302P	326	86.0	0.54	1200	471/4	660	26	11/4	38	150	56.0	123
WX-350P	450	119.0	0.39	1572	617/8	660	26	11/4	38	150	75.0	166

¹ 150 PSIG is 1034 kPa.

Max. Operating Conditions

Operating Temperature	200° F (93° C)
Working Pressure	150 PSIG (1034 kPa)

Complies with Low Lead Plumbing Law



Specifications

Description	Standard Construction	
Shell	Steel	
Diaphragm	Butyl	
Liner	Polypropylene	
System Connection	Stainless Steel NPTF	

All dimensions are approximate.

Job Name		Contractor P.O. No.	
Location _		Sales Representative	
-		Model No. Ordered	
		Pump Cut-In	_ PSI
Engineer _		Pump Cut-Out	_ PSI
Contractor		Pump GPM	_ PSI