# **Model 0012 Cartridge Circulator**

The High Velocity series Taco 0012 Cartridge Circulator is designed for high flow / medium head applications in large residential / light commercial hydronic heating, radiant heating, and chilled water cooling systems. The unique ACB anti-condensate baffle with ambient air flow prevents the build up of condensate on the motor windings when pumping chilled water. Its unique field-serviceable cartridge contains all moving parts. Replacing the cartridge rebuilds the circulator. With no mechanical seal, the self-lubricating, maintenance free design provides unmatched reliability. Compact and lightweight, with excellent performance characteristics, the 0012 is ideal for high efficiency jobs where space is a premium. Available in Cast Iron, low lead Bronze or Stainless Steel construction.



NSF<sub>®</sub> ≤ .25% Lead

Stainless Steel and Bronze Models Meet California AB 1953 and Vermont Act 193



©Taco Catalog # : 100-2.4 Supersedes: 11/20/08

## Submittal Data Information Model 0012 Cartridge Circulator

#### **Features**

- Exclusive ACB Anti-Condensate Baffle with Ambient Air Flow-Protects Motor Windings against Condensate Buildup
- High Velocity Performance-Compact Design
- Quiet, Efficient Operation
- Direct Drive-Low Power Consumption
- Unique Replaceable Cartridge Design-Field Serviceable
- Self Lubricating
- · No Mechanical Seal
- Unmatched Reliability-Maintenance Free
- · Universal Flange to Flange dimensions
- Cast Iron, low lead Bronze or Stainless Steel Construction

#### **Materials of Construction**

Casing (Volute): Cast Iron, low lead Bronze

or Stainless Steel

Stator Housing: Aluminum
Cartridge: Stainless Steel
Impeller: Non-Metallic
Shaft: Ceramic
Bearings: Carbon
O-Ring & Gaskets: EPDM

#### **Model Nomenclature**

F - Cast Iron, Flanged

 $\mathsf{BF}-\mathsf{Bronze},\mathsf{Flanged}$ 

SF - Stainless Steel, Flanged

#### **Variations:**

Z - Zoning Circulator

 $J\,$  – Bronze Cartridge with Cast Iron Casing

#### **Performance Data**

Flow Range: 0 – 52 GPM Head Range: 0 – 14.5 Feet

Minimum Fluid Temperature: 40°F (4°C)
Maximum Fluid Temperature: 230°F (110°C)
Maximum Working Pressure: 125 psi
Connection Sizes: 1-1/4", 1-1/2" or 2" Flanged



INDOOR USE ONLY

NSF® ≤ .25% Lead

Complies with California Health and Safety Code Section 116875 / AB1953 and Vermont Act 193


#### **Application**


The Taco 0012 is specifically designed for high flow / medium head applications in large residential and light commercial systems. Ideal for large BTUH Boilers, 2" recirculation loops, Primary/Secondary loops, commercial water heaters and light commercial heating and cooling systems. The Bronze or Stainless Steel 0012 can be used on open loop systems. The unique replaceable cartridge contains all of the moving parts and allows for easy service instead of replacing the entire circulator. Universal flange to flange dimensions and orientation allows the 0012 to easily replace other models. Compact, low power consumption design makes it ideal for high-efficiency jobs. The 0012-F4 is a direct replacement for the HV Series and the 0012-F4-1 is a direct replacement for the 2" Series using existing flanges.

#### Pump Dimensions & Weights • Flanges included.


Model	Flange	Casing	Α		В		С		D		F		G		Ship Wt.	
			in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	Kg
0012-F4	1-1/2"	Cast Iron	8-5/8	219	6-3/8	162	4-1/4	108	3-5/16	84	5-1/2	140	8-1/2	216	13.0	5.9
0012-SF4	1-1/2"	St. Steel	8-5/8	219	6-3/8	162	4-1/4	108	3-5/16	84	5-1/2	140	8-1/2	216	13.0	5.9
0012-F4-I	2	Cast Iron	9	229	6-3/8	162	4-1/4	108	3-5/16	84	5-1/2	140	8-1/2	216	13.0	5.9
0012-BF4-I	2	Bronze	9	229	6-3/8	162	4-1/4	108	3-5/16	84	5-1/2	140	8-1/2	216	13.0	5.9

Standard










#### **Electrical Data**

Model	Volts	Hz	Ph	Amps	RPM	HP				
All Models	115	60	- 1	1.33	3250	1/8				
Motor Type	Permanent Split Capacitor Impedance Protected									
Motor Options	220/50/1, 220/60/1, 230/60/1, 100/110/50/60/1									

### **Flange Orientation**



#### Performance Field — 60Hz

