

TruFLOW™ Jr. Valveless Manifold

Submittal Information
Revision A: April 22, 2008

Project Information

Job Name:

Location:

Part No. Ordered:

Engineer:

Date Submitted:

Contractor:


Submitted By:

Manufacturer's Representative:

Approved By:

Technical Data

Material:	UNS C3850 Brass
Manifold Body Size (i.d.):	1 ¼"
Loop Cv (valve wide open):	1.9
Manifold Body Threaded Connections:	(R32)
Manifold Loop Threaded Connections:	(R20)
Maximum Working Pressure:	145 psi
Maximum Fluid Temperature:	220°F (104°C)
Maximum Fluid Flow Rate:	14.0 gpm



Product Information and Application Use

The TruFLOW™ Jr. Valveless Manifold is used with either the TruFLOW Jr. Manifold with Isolation Valves or the TruFLOW Jr. Manifold with Balancing Valves to complete the manifold set. The TruFLOW Jr. Valveless Manifold does not feature flow balancing or isolation capability. Manifolds are available in 2-, 3- and 4-loop configurations. The manifold body ends have R32 unions and the loop outlets have R20 male threads.

✓ Description	Part Number	A	B	C	Weight
TruFLOW Jr. Valveless Manifold, 2-loop	A2663202	1.97"	5.66"	2.30"	2.10 lbs.
TruFLOW Jr. Valveless Manifold, 3-loop	A2663203	1.97"	7.63"	2.30"	2.80 lbs.
TruFLOW Jr. Valveless Manifold, 4-loop	A2663204	1.97"	9.60"	2.30"	3.40 lbs.

Installation

Refer to the AQUAPEX® Professional Plumbing Installation Handbook or Uponor Radiant Installation Handbook for additional information.

Standards

ASTM F877; R32: ISO 228-G 1 ¼; R20: ISO 228-G ¾ B

Codes

UMC; IMC; IRC; NPC of Canada

Listings

NSF; RFH

ACCESSORIES

TruFLOW Jr. Manifold Bracket - A2640006; End Cap with Vent - A2803250; Basic End Cap – A2080032

Related Applications

Radiant Heating Systems

Contact Information

Uponor, Inc.
5925 148th Street West
Apple Valley, MN 55124 USA
Phone: (800) 321-4739
Fax: (952) 891-2008
www.uponor-usa.com

Uponor Ltd.
655 Park Street
Regina, SK S4N 5N1 CANADA
Phone: (888) 994-7726
Fax: (800) 638-9517
www.uponor.ca