

Brass Manifold Pressure Test Kit

Submittal Information

Revision A: Feb. 19, 2008

Project Information

Job Name:

Location:

Part No. Ordered:

Engineer:

Date Submitted:

Contractor:

Submitted By:


Manufacturer's Representative:

Approved By:

Technical Data

Material:

360 Brass, Chrome Steel



Product Information and Application Use

The Uponor Brass Manifold Pressure Test Kit for is for use with 1½" Uponor TruFLOW™ Manifolds. Each kit contains an R32 X ¾" manifold bushing, an R32 solid brass plug, and a ¾" brass nipple and pressure gauge assembly (100 psi). A Schraeder valve is also included.

✓ Description	Part Number	A	B	C	D	Weight
Brass Manifold Pressure Test Kit	E6122000	3.03"	3.60"	¾"	R32	1.90 lbs.

Installation

Thread one end of the ¾" brass nipple into the pressure gauge assembly and the other end into the R32 x ¾" brass plug. Thread the R32 x ¾" brass plug into the inlet of the supply or return manifold. Thread the R32 solid brass plug into the inlet of the opposite manifold. Pressure the system with air to 60 psi. The system should maintain this pressure for at least 24 hours. For additional information, refer to the Uponor Radiant Installation Handbook.

Standards

N/A

Codes

N/A

Listings

N/A

Related Applications

Radiant Heating and Cooling Systems

Contact Information

Uponor, Inc.
5925 148th Street West
Apple Valley, MN 55124
USA
Phone: (800) 321-4739
Fax: (952) 891-2008
www.uponor-usa.com

Uponor Ltd.
655 Park Street
Regina, SK S4N 5N1 CANADA
Phone: (888) 994-7726
Fax: (800) 638-9517
www.uponor.ca