

## Brass Manifold Combination Adapter/Fitting Adapter


Submittal Information  
Revision A: Feb. 15, 2008

### Project Information

Job Name:	
Location:	Part No. Ordered:
Engineer:	Date Submitted:
Contractor:	Submitted By:
Manufacturer's Representative:	Approved By:

### Technical Data

Material:	CA 360 Brass
Maximum Temperature (no pressure):	220°F (104°C)
Maximum Pressure:	125 psi



### Product Information and Application Use

The Uponor Manifold Combination Adapter/Fitting Adapter connects the Uponor TruFLOW™ Manifold to copper connections in radiant heating applications.

✓ Description	Part Number	A	B	C	Weight
Brass Manifold Adapter, R32 x ¾" Adapter or 1" Fitting Adapter	A4143210	2.24"	1.75"	R32	0.62 lbs.
Brass Manifold Adapter, R32 x 1" Adapter or 1¼" Fitting Adapter	A4133210	1.98"	1.75"	R32	0.62 lbs.

### Installation

R32 threads into the Uponor TruFLOW Manifold. Copper sweats to adapter or fitting adapter. For more information, refer to the Uponor Radiant Installation Handbook.

### Standards

ASTM F877

### Codes

N/A

### Listings

NSF-rfh; R20: ISO 228-G 1¼" B

### Related Applications

Radiant Heating and Cooling Systems

### Contact Information

Uponor, Inc.  
5925 148<sup>th</sup> Street West  
Apple Valley, MN 55124  
USA  
Phone: (800) 321-4739  
Fax: (952) 891-2008  
www.uponor-usa.com

Uponor Ltd.  
655 Park Street  
Regina, SK S4N 5N1 CANADA  
Phone: (888) 994-7726  
Fax: (800) 638-9517  
www.uponor.ca