

ProPEX® Manifold Straight Adapter

Submittal Information
Revision B: Feb. 3, 2009

Project Information

Job Name:

Location:

Part No. Ordered:

Engineer:

Date Submitted:

Contractor:


Submitted By:

Manufacturer's Representative:

Approved By:

Technical Data

Material: CA 360 Brass
Maximum Temperature (no pressure): 220°F (104°C)
Maximum Working Pressure: 125 psi



Product Information and Application Use

ProPEX® Manifold Adapter for brass manifolds transitions from the R32 manifold union nut to 3/4" and 1" Uponor PEX tubing.¹

✓	Description	Part Number	A	B	C	Weight
	ProPEX Manifold Straight Adapter, R32 x 3/4" ProPEX	Q4143275	1.93"	1.75"	R32	0.60 lbs.
	ProPEX Manifold Straight Adapter, R32 x 1" ProPEX	Q4143210	2.17"	1.75"	R32	0.62 lbs.

Installation

R32 threads into the Uponor TruFLOW™ Manifold. The ProPEX end enables direct contact to Wirsbo hePEX™ plus tubing. Refer to the Uponor Radiant Installation Handbook for additional information.

Standards

ASTM F877; R32: ISO 228-G 1 1/4" B

Codes

N/A

Listings

NSF-rfh

Related Applications

Radiant Heating and Cooling Systems

Contact Information

Uponor, Inc.
5925 148th Street West
Apple Valley, MN 55124 USA
Phone: (800) 321-4739
Fax: (952) 891-2008
www.uponor-usa.com

Uponor Ltd.
2000 Argentia Rd., Plaza 1, Ste. 200
Mississauga, ON L5N 1W1 CANADA
Phone: (888) 994-7726
Fax: (800) 638-9517
www.uponor.ca

¹ProPEX® is a registered trademark of Uponor, Inc. ProPEX™ is a trademark of Uponor Ltd.