

ProPEX® Lead-free (LF) Full-port Brass Stop Valve

Submittal Information

Revision A: Jan. 20, 2009

Project Information

Job Name:

Location:

Part No. Ordered:

Engineer:

Date Submitted:

Contractor:

Submitted By:

Manufacturer's Representative:

Approved By:

Technical Data

Material:	Chrome-plated C69300 Brass
Maximum Temperature (no pressure):	140°F (60°C)
Maximum Working Temperature/Pressure:	10 to 12 seconds/3 to 4 seconds
End Switch Rating:	125 psi



Product Information and Application Use

ProPEX® Lead-free Full-port Brass Stop Valve is quarter-turn, chrome-plated and available in either angle or straight-stop configurations.¹ This stop valve is used for point-of-use shut-off at the fixture. This stop valve connects ½" AquaPEX® tubing to ¾" O.D. risers.

✓	Description	Part Number	Length	Depth	Valve Threading	Weight
	ProPEX LF Full-port Angle Stop Valve for ½" PEX	LF4855038	2.02"	1.32"	9/16" - 24 UNEF-2A	0.20 lbs.
	ProPEX LF Full-port Straight Stop Valve for ½" PEX	LF4865038	1.97"	1.33"	9/16" - 24 UNEF-2A	0.20 lbs.

Installation

Install the stop valve according to your local building code. Do not dismantle. Refer to the AquaPEX Professional Plumbing Installation Handbook or Uponor Radiant Floor Installation Handbook for additional information.

Standards

CSA B137.5 and B125; ASTM F877; ASTM F1960; ASME A112.18.1

Codes

IPC; UPC; NSPC; NPC of Canada

Listings

ANSI/NSF 14- and 61-certified; U.P. Code, Annex G

Related Applications

PEX-a Plumbing Systems
Radiant Heating and Cooling Systems
Snow and Ice Melting Systems
Permafrost Protection Systems
Turf Conditioning Systems

Contact Information

Uponor, Inc.
5925 148th Street West
Apple Valley, MN 55124 USA
Phone: (800) 321-4739
Fax: (952) 891-2008
www.uponor-usa.com

Uponor Ltd.
2000 Argentia Rd., Plaza 1, Ste. 200
Mississauga, ON L5N 1W1 CANADA
Phone: (888) 994-7726
Fax: (800) 638-9517
www.uponor.ca

¹ProPEX® is a registered trademark of Uponor, Inc. ProPEX™ is a trademark of Uponor, Ltd.