


FIG. 310CT

COPPER TUBING “EMLOK” ADJUSTABLE SWIVEL RING HANGER

FIG. 310CTI

**EPOXY COATED (COPPER-GARD) COPPER TUBING “EMLOK”
ADJUSTABLE SWIVEL RING HANGER**



- Material:** Carbon steel.
- Finish:** Copper plated (310CT) or Copper epoxy coated (*COPPER-GARD*).
- Service:** Designed for the suspension of non-insulated, stationary copper lines.
- Approvals:** Complies with Federal Specification WW-H-171-E (Type# 10), A-A-1192 A (Type# 10) and Manufacturers' Standardization Society MSS SP-58 and SP-69 (Type# 10).
- Ordering:** Specify tubing size and figure number.



TUBE SIZE	TUBE OD	MATERIAL SIZE	A	B	C	E	F	G	WGT EACH (lbs)	MAX REC LOAD (lbs)
1/2	0.625	18ga x .625	3/8	2 11/16	3	1 13/16	1 1/2	7/8	0.070	300
3/4	0.875	18ga x .625	3/8	2 1/2	2 15/16	1 5/8	1 3/16	7/8	0.070	300
1	1.125	18ga x .625	3/8	2 7/16	3	1 9/16	1	7/8	0.070	300
1 1/4	1.375	18ga x .625	3/8	2 1/2	3 3/16	1 5/8	1 5/16	7/8	0.080	300
1 1/2	1.625	18ga x .625	3/8	2 9/16	3 3/8	1 11/16	7/8	7/8	0.085	300
2	2.125	18ga x .625	3/8	3 5/16	4 3/8	2 7/16	1 3/8	7/8	0.100	300
2 1/2	2.625	14ga x 1.00	1/2	3 7/8	5 9/16	2 13/16	1 1/2	1 1/16	0.310	525
3	3.125	14ga x 1.00	1/2	4 3/16	5 3/4	3 1/8	1 9/16	1 1/16	0.345	525
3 1/2	3.625	14ga x 1.00	1/2	4 9/16	6 3/8	3 1/2	1 11/16	1 1/16	0.375	525
4	4.125	14ga x 1.00	1/2	4 13/16	6 15/16	3 3/4	1 11/16	1 1/16	0.410	650
5	5.125	14ga x 1.00	1/2	5 3/16	7 13/16	4 1/8	1 9/16	1 1/16	0.475	1000
6	6.125	14ga x 1.00	1/2	5 11/16	8 15/16	4 5/8	1 9/16	1 1/16	0.530	1000