

## For Commercial & Residential Applications

Job Name \_\_\_\_\_

Contractor \_\_\_\_\_

Job Location \_\_\_\_\_

Approval \_\_\_\_\_

Engineer \_\_\_\_\_

Contractor's P.O. No. \_\_\_\_\_


Approval \_\_\_\_\_

Representative \_\_\_\_\_


# Metal Extension Tubes




Double End Solder




Double Slip Joint



Solder



Slip joint



MODEL	✓ TO SUBMIT	DESCRIPTION	DIMENSIONS		FINISH	
			A in. mm.	B in. mm.	C	
<b>Double End Solder Type</b>						
758 503		1 1/2" x 16"	16	406	2	51
<b>Double Slip Joint Type</b>						
759 253		1 1/4" x 16"	16	406	2	51
759 503		1 1/2" x 16"	16	406	2	51
<b>Solder</b>						
710 223		1 1/4" x 6"	6	152	2	51
711 223		1 1/4" x 8"	8	203	2	51
713 221		1 1/4" x 12"	12	305	2	51
713 223		1 1/4" x 12"	12	305	2	51
714 221		1 1/2" x 6"	6	152	2	51
714 223		1 1/2" x 6	6	152	2	51
715 221		1 1/2" x 8"	8	203	2	51
715 223		1 1/2" x 8"	8	203	2	51
717 221		1 1/2" x 12"	12	305	2	51
717 223		1 1/2" x 12"	12	305	2	51
710 203		1 1/4" x 6	6	152	2	51
711 203		1 1/4" x 8"	8	203	2	51
713 203		1 1/4" x 12	12	305	2	51
717 201		1 1/2" x 12"	12	305	2	51
717 203		1 1/2" x 12"	12	305	2	51
717 171		1 1/2" x 12"	12	305	2	51
717 173		1 1/2" x 12"	12	305	2	51
<b>Slip Joint</b>						
713 32PB		1 1/4" x 12"	12	305	2	51
710 323		1 1/4" x 6"	6	152	2	51
711 323		1 1/4" x 8"	8	203	2	51
713 321		1 1/4" x 12"	12	305	2	51
713 323		1 1/4" x 12"	12	305	2	51
714 323		1 1/2" x 6"	6	152	2	51
714 323		1 1/2" x 6"	6	152	2	51
715 321		1 1/2" x 8"	8	203	2	51
715 323		1 1/2" x 8"	8	203	2	51
717 321		1 1/2" x 12"	12	305	2	51
717 323		1 1/2" x 12"	12	305	2	51
710 303		1 1/4" x 6"	6	152	2	51
711 303		1 1/4" x 8"	8	203	2	51
713 303		1 1/4" x 12"	12	305	2	51
714 303		1 1/2" x 6"	6	152	2	51
715 303		1 1/2" x 8"	8	203	2	51
717 303		1 1/2" x 12"	12	305	2	51
710 373		1 1/4" x 6"	6	152	2	51
711 373		1 1/4" x 8"	8	203	2	51
713 373		1 1/4" x 12"	12	305	2	51
714 373		1 1/2" x 6"	6	152	2	51
715 373		1 1/2" x 8"	8	203	2	51
717 373		1 1/2" x 12"	12	305	2	51

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

**WATTS®**
USA: 815 Chestnut St., No. Andover, MA 01845-6098; [www.watts.com](http://www.watts.com)

Brass &amp; Tubular Products

Canada: 5435 North Service Rd., Burlington, ONT. L7L 5H7; [www.wattscanada.ca](http://www.wattscanada.ca)

ES-WB&amp;T-Mtl-ExtTbs 0752

© Watts Regulator Company, 2007