

For Commercial & Residential Applications

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____


Approval _____

Representative _____


Metal Waste Tubes




Slip Joint Type



Quick Hook-Up Type



Slip Joint x Quick Hook-Up Type



MODEL	✓ TO SUBMIT	DESCRIPTION	DIMENSIONS			FINISH
			A in. mm.	B in. mm.	C	
Slip Joint Type						
567 221		1½" x 6"	6	152	3¼	83 22 GA. Rough Brass
570 221		1½" x 7"	7	178	3¼	83 22 GA. Rough Brass
570 222		1½" x 7"	7	178	3¼	83 22 GA. Satin
565 221		1½" x 8"	8	203	3¼	83 22 GA. Rough Brass
568 221		1½" x 9½"	9½	241	3¼	83 22 GA. Rough Brass
568 222		1½" x 9½"	9½	241	3¼	83 22 GA. Satin
571 221		1½" x 11½"	11½	292	3¼	83 22 GA. Rough Brass
571 222		1½" x 11½"	11½	292	3¼	83 22 GA. Satin
572 221		1½" x 15"	15	381	3¼	83 22 GA. Rough Brass
572 222		1½" x 15"	15	381	3¼	83 22 GA. Satin
569 221		1½" x 18"	18	457	3¼	83 22 GA. Rough Brass
573 221		1½" x 20"	20	508	3¼	83 22 GA. Rough Brass
573 222		1½" x 20"	20	508	3¼	83 22 GA. Satin
574 221		1½" x 24"	24	610	3¼	83 22 GA. Rough Brass
574 222		1½" x 24"	24	610	3¼	83 22 GA. Satin
574 221A		1½" x 24" SLIP X QHU	24	610	3¼	83 22 GA. Rough Brass
575 221		1½" x 29"	29	737	3¼	83 22 GA. Rough Brass
576 221		1½" x 36"	36	914	3¼	83 22 GA. Rough Brass
570 202		1½" x 7"	7	178	3¼	83 20 GA. Satin
571 201		1½" x 11½"	11½	292	3¼	83 20 GA. Rough Brass
571 202		1½" x 11½"	11½	292	3¼	83 20 GA. Satin
572 201		1½" x 15"	15	381	3¼	83 20 GA. Rough Brass
574 201		1½" x 24"	24	610	3¼	83 20 GA. Rough Brass
567 171B		1½" x 6" w/ brass nuts	6	152	3¼	83 17 GA. Rough Brass
571 171B		1½" x 11½" w/ brass nuts	11½	292	3¼	83 17 GA. Rough Brass
574 171B		1½" x 24" w/ brass nuts	24	610	3¼	83 17 GA. Rough Brass
Quick Hook-Up Type						
580 221		1½" x 7"	7	178	3	76 22 GA. Rough Brass
580 222		1½" x 7"	7	178	3	76 22 GA. Satin
581 221		1½" x 11½"	11½	292	3	76 22 GA. Rough Brass
581 222		1½" x 11½"	11½	292	3	76 22 GA. Satin
582 221		1½" x 15"	15	381	3	76 22 GA. Rough Brass
582 222		1½" x 15"	15	381	3	76 22 GA. Satin
583 221		1½" x 20"	20	508	3	76 22 GA. Rough Brass
583 222		1½" x 20"	20	508	3	76 22 GA. Satin
584 221		1½" x 24"	24	610	3	76 22 GA. Rough Brass
584 222		1½" x 24"	24	610	3	76 22 GA. Satin
580 202		1½" x 7"	7	178	3	76 20 GA. Satin
582 202		1½" x 15"	15	381	3	76 20 GA. Satin



815 Chestnut Street • N. Andover, MA 01845

Tel: 978.688.1811 Fax: 978.794.1848

www.wattsbrass-tubular.com

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.