



Delta BreezSmart  
Perfectly quiet. Perfectly green.

## Delta BreezSmart Series

<b>SMT130</b>	130 CFM Fan Single Speed	
<b>SMT130M*</b>	130 CFM with Motion Sensor	
<b>SMT130H*</b>	130 CFM with Humidity Sensor	
<b>SMT150</b>	150 CFM Fan Single Speed	
<b>SMT150D*</b>	Adj. 0-110/150 CFM Dual Speed	

\*M, H and D models have continuous run functionality at an adjustable low speed

## Performance meets technology with Delta BreezSmart

BreezSmart Series incorporates Delta's super reliable DC brushless motor at higher CFMs with adjustable humidity and speed, motion sensing, and a delay timer. The BreezSmart series delivers 130 CFM and 150CFM at incredibly low noise, <0.3 Sones, while consuming less than 17 Watts of power. All models have been recognized as ENERGY STAR® Most Efficient in 2014. Delta BreezSmart is a remarkable feat for residential ventilation.




Fan only & Fan with Humidity Sensor/Dual Speed




Fan with Motion Sensor

### SMT130H Controls



### SMT150D Controls



### SMT130M Controls



	Delta Breez	Market AC Motor
Energy Use (Watts)	16.9	51.3
Noise Level (Sones)	<0.3	1.4
Annual Energy Cost per Fan (24/7) <sup>1</sup>	\$17.17	\$53.94

Innovative DC brushless motor design for long life, low noise, and low power consumption

- Energy savings up to 67%<sup>2</sup>
- <0.3 sones - lowest noise level among competing fans
- Exceeds ENERGY STAR® requirement by 300% in energy efficiency<sup>3</sup>
- Motion-sensing, humidity-sensing, and dual-speed options available with user-adjustable continuous low speed

<sup>1</sup> Calculations based upon U.S. average retail electricity at and HVI testing labs. Actual results may vary

<sup>2</sup> Based upon BreezSmart SMT150 vs. market AC motor fan



<sup>3</sup> Based upon ENERGY STAR® criteria for residential ventilating fans









# Specifications

Delta BreezSmart  
Perfectly quiet. Perfectly green.

Operate your near-silent ventilation fan without lifting a finger - you just might forget it's there



Delta BreezSmart Series	SMT130* / SMT130M / SMT130H								SMT150* / SMT150D							
Fan Speed	Continuous Low Speed				Full Speed				Continuous Low Speed				Full Speed			
Static Pressure (Inches w.g.)	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25	0.1	0.25
Air Flow (CFM)	50	49	70	68	90	88	130	124	70	68	90	88	110	110	150	149
Sones	<0.3	0.7	<0.3	0.7	<0.3	0.7	<0.3	0.7	<0.3	0.7	<0.3	0.7	<0.3	0.7	<0.3	1.0
Power Consumption (Watts)	5.6	10.7	6.9	12.0	8.0	14.0	11.6	20.0	6.9	12.0	8.0	14.0	9.8	16.9	16.9	23.7
Energy Efficiency (CFM/Watt)	8.9	4.5	10.1	5.6	11.2	6.2	11.2	6.2	10.1	5.6	11.2	6.2	11.2	6.5	8.8	6.2
Current (Amps)	0.44 Max								0.47 Max							
Power Rating (V/Hz)	120/60								120/60							
Duct Diameter	6"								6"							
Automatic Operation	Yes - SMT130M  (motion sensing); SMT130H  (humidity sensing)								Yes - SMT150D (dual speed) 							
Dual Speed Operation	Yes - SMT130M  (motion sensing); SMT130H  (humidity sensing)								Yes - SMT150D (dual speed) 							
Mounting Opening	10.5" x 11.375"								10.5" x 11.375"							
Mounting Depth	7.625"								7.625"							
Grille Size	14"x14"								14"x14"							
Shipping Gross Weight (Lbs)	12.20								12.20							
cUL Tub/Shower Enclosure	Yes								Yes							
California Title 24 Compliant	Yes								Yes							
Mfg in ISO 9001 Certified Factory	Yes								Yes							
ENERGY STAR Qualified	Yes								Yes							
ENERGY STAR Most Efficient 2014	Yes								Yes							
Warranty (Years)	3								3							

\* Models SMT130 and SMT150 do not have 50, 70, 90, or 110 CFM adjustable low speed  
Design and specifications subject to change without notice.

 Adjustable motion sensor  Adjustable humidity sensor  Adjustable dual speed **Key**



4405 Cushing Parkway | Fremont, CA 94538  
tel 1.888.979.9889 | www.deltabreez.com

Delta BreezSmart Series - 10/14