




Fantech

SUBMITTAL DATA

FRD SERIES

Inline Centrifugal Fans



STANDARD FEATURES

- Galvanized steel housing with baked powder coat finish
- Powered by external rotor motor
- Permanently lubricated sealed ball bearings
- 100% speed controllable
- Automatic reset thermal overload protection
- Prewired electrical box
- Three-year factory warranty

Model	A	B	C	D	Metal Gauge	Avg Wt. (lbs)
FRD 12-6	11 7/8	5 7/8	15 3/4	11	20	17
FRD 16-8	15 3/4	7 3/4	19 3/4	15	20	30
FRD 16-8XL	15 3/4	7 3/4	19 3/4	15	20	30
FRD 20-10	19 5/8	9 3/4	20 3/8	18	20	43
FRD 24-14	23 5/8	13 3/4	28 1/2	20	20	86

All dimensions in inches.

Fan Specifications							Motor Specifications				
Line	Qty	Model No.	Tag	CFM	SP	Fan RPM	Watts	Volts	Phase	Hertz	Encl
1											
2											
3											
4											
5											

Accessory Items	1	2	3	4	5	Accessory Items	1	2	3	4	5
☐						☐					
☐						☐					
☐						☐					
☐						☐					
☐						☐					

Project: _____ Submitted: _____
 Customer: _____ Approved: _____
 Location: _____



Fantech

United States 1712 Northgate Blvd. • Sarasota, FL. 34234 • 1.800.747.1762 • www.fantech.net
Canada 50 Kanalfakt Way • Bouctouche, NB E4S 3M5 • 1.800.565.3548 • www.fantech.ca

Fantech, reserves the right to modify, at any time and without notice, any or all of its products' features, designs, components and specifications to maintain their technological leadership position.

Article #: 450372
 Rev Date: 061307