




SUBMITTAL DATA

RE(C) SERIES

Exterior-Mounted Centrifugal Fans



STANDARD FEATURES

- Galvanized steel housing with baked powder coat finish
- Powered by ebm-papst external rotor motorized impeller
- Permanently lubricated sealed ball bearings
- 100% speed controllable
- Automatic reset thermal overload protection
- Prewired electrical box
- Five-year factory warranty

Model	A	B	C	D	E	Metal Gauge	Avg Wt. (lbs)
RE 54*	4 7/8	15 1/2	9 1/2	6	1 1/2	22	11
REC 54*	4 7/8	15 1/2	9 1/2	6	1 1/2	22	11
RE 6	5 7/8	15 1/2	13 3/16	6 1/2	—	22	14
REC 6	5 7/8	15 1/2	13 3/16	6 1/2	1 1/2	22	14
RE 8XL	7 7/8	20	15 3/4	6	—	22	19
REC 8XL	7 7/8	20	15 3/4	6	1 1/2	22	19
RE 10XL	9 7/8	20	19 3/4	11 3/4	—	22	31
REC 10XL	9 7/8	20	19 3/4	11 3/4	1 1/2	22	33
RE 10XLT	9 7/8	20	20	12 1/2	—	22	33
REC 10XLT	9 7/8	20	20	12 1/2	1 1/2	22	33

All dimensions in inches.

* Models are Energy Star qualified.

Fan Specifications							Motor Specifications				
Line	Qty	Model No.	Tag	CFM	SP	Fan RPM	Watts	Volts	Phase	Hertz	Encl
1											
2											
3											
4											
5											

Accessory Items	1	2	3	4	5	Accessory Items	1	2	3	4	5
☐						☐					
☐						☐					
☐						☐					
☐						☐					
☐						☐					

Project: _____ Submitted: _____
Customer: _____ Approved: _____
Location: _____



United States 1712 Northgate Blvd. • Sarasota, FL 34234 • 1.800.747.1762 • www.fantech.net
Canada 50 Kanalfakt Way • Bouctouche, NB E4S 3M5 • 1.800.565.3548 • www.fantech.ca

Fantech, reserves the right to modify, at any time and without notice, any or all of its products' features, designs, components and specifications to maintain their technological leadership position.

Article #: 450376
Rev Date: 062007