




# SHL & SGHL Series Range Hood Liners



## READ AND SAVE THESE INSTRUCTIONS!

- Before beginning installation, please thoroughly read and become familiar with these instructions.
- Installation and service must be completed by a qualified installer.
- Failure to properly install this product may void the warranty.

**Installer:** Please leave these installation instructions with the homeowner.

**Owner:** Please keep these installation instructions for local electrical inspector's use and for future reference.

**WARNINGS:** TO REDUCE THE RISK OF FIRE, ELECTRIC SHOCK, OR INJURY TO PERSONS OBSERVE THE FOLLOWING:

- A) Use this unit only in the manner intended by the manufacturer. If you have any questions, contact the manufacturer.
- B) Before servicing or cleaning unit, switch power off at service panel and lock the service disconnecting means to prevent power from being switched on accidentally. When the service disconnecting means cannot be locked, securely fasten a prominent warning device, such as a tag to the service panel.
- C) Installation work and electrical wiring must be done by qualified person(s) in accordance with all applicable codes and standards, including fire-rated construction.
- D) Sufficient air is needed for proper combustion and exhausting of gases through the flue (chimney) or burning equipment to prevent back drafting. Follow the heating equipment manufacturer's guideline and safety standards such as those published by the National Fire Protection Association (NFPA) and the American Society for Heating, Refrigeration and Air Conditioning Engineers (ASHRAE) and the local code authorities.
- E) When cutting or drilling into wall or ceiling, do not damage electrical wiring and other hidden utilities.
- F) Duct fans must always be vented to the outdoors.

**CAUTION:** For general ventilating use only. Do not use to exhaust hazardous or explosive materials and vapors.

**WARNINGS:** TO REDUCE THE RISK OF A RANGE TOP GREASE FIRE:

- A) Never leave surface units unattended at high settings. Boil-overs may cause smoking and greasy spillovers that may ignite. Heat oils slowly on low or medium settings.
- B) Always turn hood ON when cooking at high heat or when cooking flaming foods.
- C) Clean ventilating fans frequently. Grease should not be allowed to accumulate on fan or filter.
- D) Use proper pan size. Always use cookware appropriate for the size of the surface element.

**WARNING:** TO REDUCE THE RISK OF INJURY TO PERSONS IN THE EVENT OF A RANGE TOP GREASE FIRE, OBSERVE THE FOLLOWING:

- A) SMOTHER FLAMES with a close-fitting lid, cookie sheet or metal tray, then turn off the burner. BE CAREFUL TO PREVENT BURNS. If the flames do not go immediately, EVACUATE AND CALL THE FIRE DEPARTMENT.
- B) NEVER PICK UP A FLAMING PAN You may be burned.
- C) DO NOT USE WATER, including wet dishcloths or towels – a violent steam explosion will result.
- D) Use an extinguisher ONLY if:
  1. You know you have a Class ABC extinguisher, and you already know how to operate it.
  2. The fire is small and contained in the area where it started.
  3. The fire department is being called.
  4. You can fight the fire with your back to an exit.

## PART 1 Planning the Installation

### CAUTION:

1. To reduce the risk of fire and to properly exhaust air, the liner must be exhausted to the outside. Never exhaust into a wall, an attic or a concealed area in the building. This can create a potential hazard.
2. Consult a licensed ventilation contractor or qualified technician for proper installation of exhaust ducting.
3. Locate the cooking area for minimum cross drafts – away from doors and windows, when possible.
4. Ducts must be of adequate size and duct runs should be as short as possible. Where turns are necessary, keep turning radius as large and as smooth as possible.
5. The ducting must be air tight. Use a minimum of 2 sheet metal screws at every duct joint. Then, seal the duct joints with high quality duct tape.
6. Only use ductwork constructed of materials deemed acceptable by state, municipal and local codes.

### NOTES:

- The hood liner is designed to install inside a custom hood enclosure and operates with a remote mount blower (purchased separately). See dimensional drawings (page 3) for hood dimensions. See chart (page 3) for Fantech exhaust fans recommended for use with these units.
- A qualified person must complete the installation of this appliance.
- Plan the installation so that all minimum clearance are met or exceeded.
- **IMPORTANT:** You must provide support framing and backing in the areas in which you are securing the liner to in your custom canopy. Failure to do so could damage the liner and void the warranty.

## PART 1 Planning the Installation (continued)

### NOTES:

1. The hood liner uses 120VAC, 60 Hz power. Supply wires should be installed by a qualified person(s) and must meet all electrical codes. The SGHL30 & SGHL36 Hood Liners are designed for use with 6" diameter duct, the SHL36 & SHL42 are designed for use with 8" diameter duct and the SHL48 is designed for use with 10" diameter duct. *Use only rigid metal duct.*
2. For a truly quiet kitchen ventilation system add a Fantech "duct silencer" (LD Series) to the installation. The simple addition of an inline duct silencer between the hood liner and the remote fan can typically reduce the "perceived" sound level of the system by more than 50%. For more information visit [www.fantech.net](http://www.fantech.net).
3. A quality cap with built in backdraft damper or an inline damper is recommended to minimize cold air return through the duct when the product is not in use.
4. Always install ventilation products with an approved wall or roof cap.
5. Duct performance is improved by using round, smooth metal duct work instead of rectangular.
6. If multiple elbows must be used, ensure that there is a minimum of 24" of straight duct between any two elbows.
7. Avoid "S" or back to back configurations caused by adjacent elbows.
8. Route ducting to terminate at the hood liner.

**WARNINGS:** Following Are Manufacturer's Suggestions. Always Observe Local Building Codes.

1. Liners installed in custom canopies constructed of combustible materials, should be installed with the combustible material structure a minimum of 36" above the surface of the heating element.
2. Liners installed in custom canopies constructed of non-combustible materials, should be installed with the non-combustible material structure a minimum of 30" above the surface of the heating element.
3. Follow all instructions regarding minimum safe clearances and installation location. Failure to do so may result in a safety hazard or fire.
4. To reduce the risk of fire use only metal ductwork.

### CHOOSING THE RIGHT REMOTE MOUNT BLOWER (see page 3)

Look on page 3 for a list of Fantech fans recommended for use with the SHL & SGHL Series Range Hood Liners. Some models remotely mount in the attic. Other models are used when installation requires a roof mount or wall mount fan.

## PART 2 Electrical Connection

### WARNINGS:


1. Ensure that the power supply is disconnected before proceeding.
  2. Verify that the power supply matches the ratings found on the appliance data label before proceeding.
  3. The complete appliance must be properly grounded at all times when electrical power is applied.
  4. Do not ground the appliance with the neutral (white) house supply wire. A separate ground wire must be utilized.
  5. Failure to complete electrical connections properly may result in damaged or non-functional systems. Follow instructions carefully to ensure proper installation.
- It is the owner's responsibility to ensure that a qualified electrician performs the electrical connection of this appliance. The electrical installation, including minimum supply wire size, must comply with the National Electric Code ANSI/NFPA 70-1990 (or latest revision) and local codes and ordinances.
  - A copy of this standard may be obtained from: National Fire Protection Association, 1 Batterymarch Park Quincy, Massachusetts 02269-9101

### INSTRUCTIONS:

1. A 15 to 20 amp electrical service is recommended for proper electrical supply. Before determining, calculate amp ratings based on the product label found on the liner and the ventilator. (Always observe local building codes).
2. Always use a dedicated circuit.
3. Line load is calculated by adding the amperage of the halogen lights to the rated amperage of the ventilator (either in-line or roof top). If the ventilator is rated in watts rather than amps, divide the watts by 120 and this will give you the amperage rating.
4. The Fantech liner is supplied with a 5.0 amp variable speed fan control. Make sure the rated amperage on the ventilator does not exceed 5.0 amps. For larger ventilators rated above 5.0 amps, contact Fantech Customer Service for recommendations.
5. The Fantech liner has been designed to accommodate several different motor speed controls, (for example Thermador™ model CTR3-Q) Always consult the manufacturer's installation instructions when substituting control switches.
6. Wire connections (see internal wiring schematic):
  - Black - 120 VAC from electrical panel (black)
  - White - Neutral from electrical panel (white)
  - Green - Ground from electrical panel (green)
  - Red - 120 VAC variable control to 120 VAC of ventilator

### CAUTION:

The neutral wire (usually white) for the ventilator must connect to the same neutral wire that comes from the electrical panel to the liner. It is recommended to run a white neutral wire from the liner's white neutral wire along the same path as the red wire from the liner's variable speed control to the ventilator.



## PART 3 Securing the Liner


### SECURING INSTRUCTIONS:

1. Because the professional series liner was designed for custom applications, no mounting holes have been pre-drilled. This allows you to attach the liner in the areas of the canopy which have ample support and backing.
2. You must secure the liner through both right and left sides, through the back and through the top.
3. Remove the filters. Mark and drill screw holes through the liner as required for custom canopy. Secure the liner by driving screws (provided by others) through the liner into the framing and backing.

### CONNECTING TO THE VENT PIPE:


1. Insert the tabbed end of the galvanized start collar into the round hole in the outside top of the liner.
2. Bend all of the tabs firmly in places against the inside top of the liner. Sheet metal screws should be placed equidistant through 3 or more tabs. **CAUTION:** for safety of the person cleaning this liner, neatly cover the well-flattened tabs with 2 or more layers of metal tape.
3. Attach the other end of the start collar to the range hood vent with a minimum of 3 equidistant screws and metal tape.

**Dimensions** - All dimensional tolerances are 0" to 1/16 unless otherwise stated



Model	UPC#	Duct <sup>†</sup>	A	B	C	E
SHL36	47036	8	34 1/2	22	6	3
SHL42	47042	10	40 1/2	22	6	3
SHL48	47048	10	46 1/2	22	6	3

**SGHL 30 & SGHL 36 Dimensions**



Model	UPC#	Duct <sup>†</sup>	A	B	C	E
SGHL30	47530	6	28 1/2	18	4	3
SGHL36	47536	8	34 1/2	18	4	3

**Choosing the right remote mount blower**

**SHL36**

Model	Location	Mounting	Airflow at 0"	Typical Airflow <sup>†</sup>
FX 8	interior	inline	481	430
FX 8XL	interior	inline	521	480
FKD 8XL	interior	inline	836	740
FKD 10XL	interior	inline	1266	1175
RVF 8XL	exterior	wall	435	392
RE 8XL	exterior	roof/wall	409	356
RE 10XL	exterior	roof/wall	753	730

**SGHL30**

Model	Location	Mounting	Airflow at 0"	Typical Airflow <sup>†</sup>
FX 6*	interior	inline	257	190
FX 6XL	interior	inline	392	275
FX 8XL	interior	inline	521	320
RE 6*	exterior	roof/wall	227	205
RE 8XL	exterior	roof/wall	409	356
RVF 6*	exterior	wall	242	200
RVF 6XL	exterior	wall	381	330

**SHL42**

Model	Location	Mounting	Airflow at 0"	Typical Airflow <sup>†</sup>
FX 8	interior	inline	481	430
FX 8XL	interior	inline	521	480
FKD 8XL	interior	inline	836	740
FKD 10XL	interior	inline	1266	1175
RVF 8XL	exterior	wall	435	392
RE 8XL	exterior	roof/wall	409	356
RE 10XL	exterior	roof/wall	753	730

**SGHL36**

Model	Location	Mounting	Airflow at 0"	Typical Airflow <sup>†</sup>
FX 8XL	interior	inline	521	320
FKD 8XL	interior	inline	836	740
RE 8XL	exterior	roof/wall	409	356
RE 10XL	exterior	roof/wall	753	730
RVF 8XL	exterior	wall	435	392

**SHL48**

Model	Location	Mounting	Airflow at 0"	Typical Airflow <sup>†</sup>
FX 10	interior	inline	521	470
FX 10XL	interior	inline	590	540
FKD 10	interior	inline	910	780
FKD 10XL	interior	inline	1266	1060
FKD 12XL**	interior	inline	2016	1460
RE 10XL	exterior	roof/wall	753	720

<sup>†</sup> Typical airflow is an estimate based on a system with 20' of duct, two 90° elbows, a backdraft damper, roof cap and filters.

\* Fans will meet most local code requirements but will produce less than Fantech's recommended ventilation rate of 100 cm per foot of hood width.

\*\* Requires larger speed control. Contact Fantech Customer Service for recommendations.

## PART 4 Use & Care

### OPERATING CONTROLS:

1. Always activate the ventilator whenever using cooking appliances.
2. Activate the ventilator a few minutes before starting to cook to establish an airflow pattern within the room.
3. Adjust the fan speed according to the amount of cooking exhaust.
4. Adjust the dimmable halogen lights as desired.
5. Eliminate air currents in the hood vicinity by shutting nearby windows and doors, turning off ceiling fans and closing the adjacent heating and air conditioning outlets.
6. Place your largest pans, skillets and stock pots on the rear burners whenever possible.

**WARNING:** DO NOT operate the vent system without the filters in place, or with dirty, grease laden filters.

### ENERGY SAVING TIPS:

1. Do not operate the blower at a speed that is higher than necessary to remove the cooking exhaust. Running at excessive speeds removes more air from the inside of the house that must be replaced by outside air. This may be especially costly when your home's heating or air conditioning system is in operation. Turn off the unit once the smoke and cooking odors have been eliminated.
2. Clean filters and grease laden surfaces often to improve efficiency.
3. Always use lids on cookware to retain heat and moisture.
4. Minimize the amount of liquid used to cook food.
5. Select cookware of proper size, material and construction for the cooking task being performed.

### CARE & CLEANING:

1. Proper cleaning is necessary to maintain performance and appearance, while also ensuring safe operation. The frequency of cleaning should be adjusted according to the type and amount of cooking. Best results will be achieved by cleaning soiled components as soon as possible.
2. Filters must be cleaned regularly.  
SHL Series: Remove one filter at a time, grasp the filter handle and gently pull toward you, then down and back. Filter should be installed with the handle in the rear filter slot.  
SGHL Series: Remove one filter at a time. Insert a blunt knife into the small slot in the front edge of the filter. Push down and back. Filter should be installed with small slot at the front of the filter.
3. The filters may be cleaned by hand washing in hot water using a mild detergent solution, or by placing them in the top rack of an automatic dishwasher. Dry the filters completely before using again.
4. Stainless steel surfaces should be cleaned with a solution of mild detergent and warm water. Rinse and dry with a soft lint-free cloth.  
**CAUTION:** Do not use any type of pad that will scratch the liner
5. **CAUTION:** If a commercially available stainless steel cleaner is used. It is important to read the labels for chlorine compounds. Chlorine is a corrosive substance. If these compounds are present, rinse thoroughly and dry with a soft lint-free cloth. Follow polish manufacturer's instructions.
6. Always wipe stainless steel surfaces with the grain. Never wipe across the grain.
7. After cleaning, reinstall the filters carefully.

**REPLACING LIGHT BULBS:** Par 20 halogen lamps are available in many different styles and sizes. Following is a list recommended by the manufacturer:

- Philips MASTER Line 50 watts 120V
- Felt Electric 50 watt 130V
- Industrial Grade Premium Quality™ P.Q.L. Incorporated Code 83009

**REPLACEMENT FILTERS:** Order online at [www.fantech.net](http://www.fantech.net)



### FIVE YEAR WARRANTY

#### DURING ENTIRE WARRANTY PERIOD:

FANTECH, INC. will repair or replace any product which has a factory defect in workmanship or material. Product may need to be returned to the FANTECH factory, together with a copy of the bill of sale and identified with RMA number.

#### THE FOLLOWING WARRANTIES DO NOT APPLY:

- Damages from shipping, either concealed or visible. Claim must be filed with freight company.
- Damages resulting from improper wiring or installation.
- Damages or failure caused by acts of God, or resulting from improper consumer procedures, such as:

1. Improper maintenance
  2. Misuse, abuse, abnormal use, or accident, and
  3. Incorrect electrical voltage or current.
- Removal or any alteration made on the FANTECH label control number or date of manufacture.
  - Any other warranty, expressed, implied or written, and to any consequential or incidental damages, loss or property, revenues, or profit, or costs of removal, installation or reinstallation, for any breach of warranty.

#### WARRANTY VALIDATION

- The user must keep a copy of the bill of sale to verify purchase date.
- These warranties give you specific legal rights, and are subject to any applicable consumer protection legislation. You may have additional rights which vary from state to state.

#### United States

1712 Northgate Blvd. • Sarasota, FL 34234  
(T) 1.800.747.1762 • (F) 1.800.487.9915  
(T) 1.941.309.6000 • (F) 1.941.309.6099  
web: [www.fantech.net](http://www.fantech.net) • email: [info@fantech.net](mailto:info@fantech.net)

#### Canada

50 Kanalfakt Way, Bouctouche, NB E4S 3M5  
(T) 1.800.565.3548 • (F) 1.800.747.8116  
(T) 1.506.743.9500 • (F) 1.506.743.9600  
web: [www.fantech.ca](http://www.fantech.ca) • email: [info@fantech.ca](mailto:info@fantech.ca)