# Liberty Fumps



#### SINGLE PHASE

208-230V, 15a, manual **LEH152M** LEH152A 208-230V, 15a, automatic

**3-PHASE** 

208-230V, 10.6a, manual\* LEH153M LEH154M 440-480V. 5.3a. manual\* 575V, 4.8a, manual\* LEH155M

\*Note: 3-phase models require control panel for automatic operation. See sewage accessories literature for complete information on all simplex and duplex controls.

## High Head Sewage **Pumps**

1.5 hp 2" Solids-Handling 2" or 3" Flanged **Discharge** 70' Maximum TDH

#### Features:

- Rugged 2 vane, semi-open cast iron impellers
- Cast iron housing and volute with all stainless fasteners
  - 416 stainless steel rotor shaft
- Oil-filled, hermetically sealed motors
- Built-in thermal protection on single phase models
  - 2" or 3" flanged discharge
  - Permanently lubricated upper and lower ball bearings
    - Dual shaft seals
- Single float mechanical level control with series plug for manual bypass operationstandard on single-phase automatic models
- Quick-disconnect 25<sup>1</sup> standard power cord allows replacement of cord in seconds without breaking seals to motor

# LEH150-SERIES TECHNICAL SPECIFICATIONS

#### **PUMP**

The pump(s) shall be model	as manufac-			
tured by Liberty Pumps, Bergen, N.Y. or equal. The pump(s)				
shall have a capacity of GPM at a to	otal dynamic head			
of feet. Motor size shall be 1.5 horsepower,				
phase, 60 hz. and volt op	eration.			

#### **MOTOR**

The pump motor shall be class B of the submersible type, oil filled, and hermetically sealed. Single phase motors shall have thermal overload protection embedded in the windings, and shall automatically reset when motor cools. Three-phase motors shall have heatbreakers incorporated into the control panel, properly sized for the horsepower and amperage of the pump(s).

The rotor shaft shall be made of 416 stainless steel and shall be supported by upper and lower ball bearings.

The power cord shall be of the quick-disconnect design.

#### **IMPELLER**

The pump impeller shall be cast iron, 2 vane, semi-open, and shall be capable of passing a 2" spherical solid.

#### **DUAL SHAFT SEAL**

Upper seal shall be unitized silicon carbon and the lower seal shall be Viton double lip.

#### **EXTERNAL CONSTRUCTION**

The pump volute, legs and motor housing shall be heavy gray iron castings, class 25 or better. All castings shall be powder coated before assembly.

All fasteners shall be of 300-series stainless steel.

#### LEVEL CONTROL

The pump shall be controlled by an adjustable mechanical switch sealed in a PVC float, and shall have a series plug for manual bypass operation. (Single phase model only)

### ALL MODELS: 1.5 HP, 3450 RPM

MODELS	<b>VOLTS</b>	PHASE	<b>AMPS</b>	DISCHARGE	<b>AUTOMATIC</b>
LEH152M2	208-230	1	15	2" FLANGED	NO
LEH152M3	208-230	1	15	3" FLANGED	NO
LEH152A2	208-230	1	15	2" FLANGED	YES
LEH152A3	208-230	1	15	3" FLANGED	YES
LEH153M2	208-230	3	10.6	2" FLANGED	NO
LEH153M3	208-230	3	10.6	3" FLANGED	NO
LEH154M2	440-480	3	5.3	2" FLANGED	NO
LEH154M3	440-480	3	5.3	3" FLANGED	NO
LEH155M2	575	3	4.8	2" FLANGED	NO
LEH155M3	575	3	4.8	3" FLANGED	NO
	LEH152M2 LEH152M3 LEH152A2 LEH152A3 LEH153M2 LEH153M3 LEH154M2 LEH154M3 LEH154M3	LEH152M2 208-230 LEH152M3 208-230 LEH152A2 208-230 LEH152A3 208-230 LEH153M2 208-230 LEH153M3 208-230 LEH154M2 440-480 LEH154M3 440-480 LEH155M2 575	LEH152M2 208-230 1 LEH152M3 208-230 1 LEH152A2 208-230 1 LEH152A3 208-230 1 LEH153M2 208-230 3 LEH153M3 208-230 3 LEH154M2 440-480 3 LEH154M3 440-480 3 LEH155M2 575 3	LEH152M2       208-230       1       15         LEH152M3       208-230       1       15         LEH152A2       208-230       1       15         LEH152A3       208-230       1       15         LEH153M2       208-230       3       10.6         LEH153M3       208-230       3       10.6         LEH154M2       440-480       3       5.3         LEH154M3       440-480       3       5.3         LEH155M2       575       3       4.8	LEH152M2       208-230       1       15       2" FLANGED         LEH152M3       208-230       1       15       3" FLANGED         LEH152A2       208-230       1       15       2" FLANGED         LEH152A3       208-230       1       15       3" FLANGED         LEH153M2       208-230       3       10.6       2" FLANGED         LEH153M3       208-230       3       10.6       3" FLANGED         LEH154M2       440-480       3       5.3       2" FLANGED         LEH154M3       440-480       3       5.3       3" FLANGED         LEH155M2       575       3       4.8       2" FLANGED

NOTE: 3-Phase models require panel for automatic operation. See sewage accessories literature for complete information on all simplex and duplex controls.

#### **DIMENSIONAL DATA:**

Weight: LEH152M: 92 LBS.

Height: 21"

Major Width: 13"

Maximum fluid temperature: 140 degrees F.

NOTE: LEH150-Series high-head pumps

require a minimum head of 20'.

## PERFORMANCE CURVE 60hz



