

Air Conditioning & Heating

DSXC18 HIGH-EFFICIENCY AIR CONDITIONERS







Energy Star ratings are dependent upon conditions beyond equipment installation. To make certain your HVAC equipment qualifies for the Energy Star designation, get complete information at www.energystar.gov.

Thank goodness for Goodman®



Air Conditioning & Heating

ENERGY-SAVING EFFICIENCY WITH GOODMAN

When properly matched and installed, your Goodman® brand DSXC18 Air Conditioner offers up to 18 SEER high-efficiency performance. "SEER" stands for Seasonal Energy Efficiency Ratio, a measure used by the U.S. Department of Energy to rate the efficiency of air conditioners. The higher the SEER, the greater the efficiency — and the lower the operating cost. In many applications, the efficiency of your Goodman brand DSXC18 Air Conditioner can be enhanced by using it in conjunction with a Goodman brand gas furnace that includes a variable-speed blower motor. Talk to your Goodman dealer about opportunities to optimize the efficiency of your new unit.



COMFORT. SAVINGS. PERFORMANCE.

ENJOY THE COMFORT OF A GOODMAN BRAND AIR CONDITIONER

Beat the summer heat with a Goodman brand DSXC18 R-410A Air Conditioner — a unit that provides you with high efficiency, reliable performance and quiet operation. This air conditioner's worry-free operation and outstanding features add up to outstanding comfort and energy-saving value compared to lower SEER units.

EXPERIENCE QUIET COMFORT

You can be assured that your Goodman brand air conditioner will provide you with quiet cooling all year long. To minimize operating sounds, we've acoustically engineered our systems with enhancements that include a compressor sound-reduction cover made of high-density foam and a specially designed wire discharge grille. Additionally, the two-speed operation of the condenser fan motor allows your outdoor fan to run more often at a lower speed.



COMMITMENT TO QUALITY ENGINEERING

Always in pursuit of the highest performance and efficiency, our

engineers are constantly evaluating the latest and most reliable technology and applying it to every Goodman brand air conditioner.

But best of all, your new air conditioner is compatible with the ComfortNetTM system of communicating products. With a large assortment of built-in features, your contractor can autoconfigure, monitor and review data from the system. This allows for optimum performance and accurate detection of any system-related issue.

R-410A REFRIGERANT

Compared to the lower SEER R-22 refrigerant units, your new Goodman brand DSXC18 air conditioning system will not only provide you with money-saving cooling performance for many years, but it also features R-410A refrigerant. Since this refrigerant does not contain chlorine, it is more environmentally friendly than R-22 refrigerant.

Introduced in 1995, R-410A refrigerant has helped increase the durability and reliability of air conditioner compressors.





IMPRESSIVE FEATURES & BENEFITS:

GOODMAN® BRAND DSXC18

R-410A HIGH-EFFICIENCY AIR CONDITIONER

- High-efficiency cooling performance
- ComfortNet™ Communicating Systems compatible
- Chlorine-free R-410A refrigerant
- Two-stage UltraTech Copeland® scroll compressor
- Expanded ComfortAlert™ diagnostics built in
- 5mm SmartCoil™ condenser coil in select models
- A louvered cabinet made of heavy-gauge galvanized steel that protects the coil
- High- and low-pressure switches

- Quiet operation ensured by:
 - A high-density foam compressor sound cover
 - Efficient condenser fan motor
 - A wire fan discharge grille
- Factory-installed, liquid line filter drier
- Factory-installed ambient temperature sensor
- Appliance-quality, post-paint finish resists the effects of weather and time
- Air Conditioning, Heating, and Refrigeration Institute (AHRI) certified

Talk to your Goodman® brand dealer about opportunities to optimize the efficiency of your new unit.

OUTSTANDING WARRANTY* PROTECTION







* Complete warranty details available from your local dealer or at www.goodmanmfg.com. To receive the 10-Year Unit Replacement Limited Warranty, Lifetime Compressor Limited Warranty (good for as long as you own your home), and 10-Year Parts Limited Warranty, online registration must be completed within 60 days of installation. Online registration is not required in California or Quebec.

ADDITIONAL INFORMATION

Before purchasing this appliance, read important information about its estimated annual energy consumption, yearly operating cost, or energy efficiency rating that is available from your retailer.



Thank goodness for Goodman:

MODEL	COOLING EFFICIENCY SEER	LIMITED PAR	LIFETIME COMPRESSOR	COVERAGE PARTS YEAR PARTS UMITED WARRANTY	COMPATIBLE	COMPRESSOR SOUND BLANKET	FACTORY- INSTALLED FILTER DRYER	energy STAR
DSXC18	Up to 18	•	•	•	•	•	•	•
DSXC16	Up to 16	•	•	•	•	•	•	•
SSX16	Up to 16		•	•		•	•	•
SSX14	Up to 15		•	•		•	•	•
GSX13	13			•			•	

^{*} Complete warranty details available from your local dealer or at www.goodmanmfg.com. To receive the 10-Year Unit Replacement Limited Warranty, Lifetime Compressor Limited Warranty (good for as long as you own your home) and 10-Year Parts Limited Warranty, online registration must be completed within 60 days of installation. Online registration is not required in California or Quebec.



** ENERGY STAR ratings are dependent upon conditions beyond equipment installation. To make certain your HVAC equipment qualifies for the ENERGY STAR designation, get complete information at www.energystar.gov.

GOODMAN: THE RECOGNIZED INDUSTRY LEADER

Every Goodman® brand heating and air conditioning system is designed, engineered, and manufactured with pride. All employees follow strict, quality-driven processes to ensure that all Goodman products offer the legendary performance that has made the brand a recognized leader in the industry. This attention to quality has resulted in the Goodman family of companies becoming the second largest unit manufacturer of residential air conditioning and heating systems in North America.

THE GOODCARE® EXTENDED SERVICE PLAN

For even greater peace of mind, ask your dealer or visit our website at **www.goodmanmfg.com** for more details about **GoodCare,** an affordable Parts and Labor Extended Service Plan for your entire Goodman brand HVAC system.†

† Extended Service Plans not available in all states. Ask your dealer for full details.







Air Conditioning & Heating

Our continuing commitment to quality products may mean a change in specifications without notice.

© 2011 Goodman Manufacturing Company, L.P. · Houston, Texas





