

Viega® ProPress and ProPress XL (Copper) Fitting Systems

ProPress® and ProPress XL (Copper) are safe, reliable and economical copper pipe installation systems that use modern cold press connection technology.

Viega® ProPress fittings are for use with type K, L and M hard copper tubing from ½" to 4" and soft copper tubing in ½" to 1¼" diameters. All tubing must comply with the ASTM B88 standard. ProPress fittings are approved for installations in both above and below ground applications. Per code, local inspector approval must be obtained prior to installation below ground.

ProPress has been used in Europe since the late 1980s and in the United States since the late 1990s for a variety of applications. Backed by two plumbing leaders with over 175 years of combined excellence.

Listings and Certificates

- NSF 61G
- IAPMO PS117
- UL 213
- FM Class 1920
- ICC-ES PMG 1037
- CSA MSE-13
- ABS

International Listings and Certificates

- Deutsch Verein des Gas-und Wasserfachese.V. (DVGW)
- Lloyd's Register (LR)
- Det Norske Veritas (DNV)
- Registro Italiano Navale (RINA)
- Bureau Veritas (BV)
- KIWA

Compliant with:

- ICC International Plumbing Code
- IAPMO Uniform Plumbing Code
- PHCC National Standard Plumbing Code
- Florida Building Code, Volume II Plumbing Code
- NFPA 13, 13D and 13R
- ASME B16.51
- U.S. Coast Guard

Viega ProPress fittings are offered in configurations including: Elbows, Couplings, Reducers, Tees, Reducing Tees, Threaded Adapters, Unions, Caps and Flanges. All threaded ½" to 2" fittings are Zero Lead bronze.

Operating Parameters

Operating Pressure: 200 PSI maximum
Test Pressure: 600 PSI maximum
Operating Temperature: 0°F to 250°F



Approved Applications:

- Potable Water
- Hydronic Heating (w/ Glycol)
- Chilled Water
- Compressed Air (200 PSI maximum)
- Non-medical Gases (140 PSI maximum)
- Fire Sprinkler (175 PSI maximum)
- Low Pressure Steam (15 PSI maximum)
- Vacuum (29.2 in. Hg maximum @ 68°F)

In ProPress ½" to 4" dimensions, the Smart Connect Feature assures leakage of liquids and/or gases from inside the system past the sealing element of an unpressed connection. The function of this feature is to provide the installer quick and easy identification of connections which have not been pressed prior to putting the system into operation.

Recommended Tools:

- RIDGID RP 200-B (½" to 1¼")
- RIDGID RP 210-B (½" to 1¼")
- RIDGID RP 330-B or 330-C
- RIDGID RP 340

Contact your local Viega representative for details on local approvals.