



Submittal Data Information

3-Speed Cartridge Circulator

100-51

Effective: April 2, 2012

Supersedes: June 24, 2011

Job: _____ Engineer: _____ Contractor: _____ Rep: _____

ITEM NO.	MODEL NO.	IMP. DIA.	G.P.M.	HEAD/FT.	H.P.	ELEC. CHAR.

Features

- 3-Speed Switch
- Fine tune to system requirements
- Highest performance & starting torque in class
- Heavy duty construction for longer life
- 4-bolt universal flange (0010 only)
- Removable high-flow Integral Flow Check (IFC*)
 - Prevents gravity flow
 - Reduces installation costs
 - Improves pump performance
- Replaceable cartridge design
- Quiet, efficient operation
- Self lubricating, no mechanical seal
- Wide range of applications
- Cast Iron or Stainless Steel, flanged construction

Materials of Construction

Casing:.....0015
(Cast Iron or Stainless Steel)

Casing:.....0010
(Only Cast Iron)

Integral Flow Check (IFC*):
Body, Plunger.....Acetal
O-ring Seal.....EPDM
Spring.....Stainless Steel

Stator Housing:.....Steel

Cartridge:.....Stainless Steel

Impeller:.....Non-Metallic

Shaft:.....Ceramic

Bearings:.....Carbon

O-Ring & Gaskets:.....EPDM

Model Nomenclature

F – Cast Iron, Flanged
SF – Stainless Steel, Flanged
MS – 3-Speed Switch
IFC – Integral Flow Check

Performance Data

	0015	0010
Flow Range (GPM):	0-18	0-29
Head Range (FT):	0-21	0-10.5
Minimum Fluid Temperature:	40°F (4°C)	
Maximum Fluid Temperature:	230°F (110°C)	
Maximum Working Pressure:	125 psi	
Connection Sizes:	3/4", 1", 1-1/4", 1-1/2" Flanged	

NSF® ≤ .25% Lead

Complies with California Health and Safety Code Section 116875 / AB1953 and Vermont Act 193



FOR INDOOR USE ONLY

Application


The 0015 3-Speed pump is specifically designed for the wide range of flow and head requirements of today's hydronic heating systems. Its 3-Speed switching capability provides fine tuning control to match a wide combination of tube diameters and length of runs. The 0015 3-Speed is a direct replacement for the Grundfos UPS 15-58 3-Speed. The 0015 delivers the highest starting torque in its class and includes a removable, uni-body Integral Flow Check (IFC*) that prevents gravity flow, reduces installation costs and improves pump performance. The Stainless Steel 0015 should be used on open, fresh water systems.

The 0010 3-Speed Service pump is designed as an ideal replacement circulator for service contractors to use on any emergency "no-heat" call. The 0010 3-Speed replaces most commonly used circulators. Simply install it and set the speed to match the original pump performance. The handy new four bolt flange matches up to any pump regardless of style, type or age.


Pump Dimensions & Weights

Models	Flange Code	A		B		C		D		F		G		Ship Wt.	
		in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	Kg
0015-MSF2-IFC	S	6-1/2	165	4-5/8	118	3-3/16	81	3-7/16	78	5-3/8	137	6-3/8	162	8	3.5
0015-MSSF2-IFC*	S	6-1/2	165	4-5/8	118	3-3/16	81	3-7/16	78	5-3/8	137	6-3/8	162	8	3.5
0015-MSF2-1 IFC	R	6	152	4-5/8	118	3-3/16	81	3-7/16	78	5-3/8	137	6-3/8	162	8	3.5
0015-MSSF2-1 IFC*	R	6	152	4-5/8	118	3-3/16	81	3-7/16	78	5-3/8	137	6-3/8	162	8	3.5
0010-MSF1-IFC	U	6-11/16	170	4-3/4	120	3-3/16	81	3-7/16	78	5-3/8	137	6-3/8	162	10	4.5

* Stainless Steel



Mounting Positions




Electrical Data

Model	Volts	Hz	Ph	Amps			RPM (Speed 3)	HP
				Speed 1	Speed 2	Speed 3		
0015	115	60	1	.71	.82	.98	3250	1/20
0010	115	60	1	.75	.91	1.10	3250	1/20

Motor Type: Permanent Split Capacitor Thermally Protected

Performance Field - 60Hz



Flange Orientation

