

For Commercial & Residential Applications

Job Name _____
 Job Location _____
 Engineer _____
 Approval _____

Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____


KwikStop®

Quarter-Turn Water Supply Stops

Sizes: $\frac{3}{8}$ - $\frac{5}{8}$ " (10 – 17mm)

Features

- "Kwik" quarter-turn "On" or "Off"
- Ball valve style construction
- Available in straight and angle configurations
- Large, conventional handles
- Chrome-plated brass construction with PTFE seats
- Complies with NSF 61 Section 9
- Nuts and ferrules assembled
- Packaged in convenient window boxes; kits in plastic bags
- IAPMO Listed



MODEL NO.	✓ TO SUBMIT	TYPE	DESCRIPTION	DIMENSIONS		FINISH	
				A in mm	B in mm	C in mm	
BV889013		Straight	$\frac{3}{8}$ " IPS x $\frac{3}{8}$ " OD Comp	1 $\frac{3}{16}$ 46	1 $\frac{1}{16}$ 18	1 $\frac{5}{16}$ 50	Chrome
BV892413		Straight	$\frac{1}{2}$ " CPVC x $\frac{3}{8}$ " OD Comp	1 $\frac{3}{16}$ 46	1 $\frac{1}{16}$ 18	2 $\frac{5}{8}$ 66	Chrome
BV891313		Straight	$\frac{1}{2}$ " PEX x $\frac{1}{2}$ " PEX	1 $\frac{3}{16}$ 46	$\frac{1}{2}$ 12	2 $\frac{3}{16}$ 56	Chrome
BV890013		Straight	$\frac{1}{2}$ " IPS x $\frac{3}{8}$ " OD Comp	1 $\frac{3}{16}$ 46	1 $\frac{1}{16}$ 18	2 $\frac{1}{16}$ 52	Chrome
BV892013		Straight	$\frac{1}{2}$ " Copper Sweat x $\frac{3}{8}$ " OD Comp	1 $\frac{3}{16}$ 46	1 $\frac{1}{16}$ 18	2 $\frac{1}{2}$ 63	Chrome
BV894013		Straight	$\frac{5}{8}$ " OD Comp x $\frac{3}{8}$ " OD Comp	1 $\frac{3}{16}$ 46	1 $\frac{1}{16}$ 27	2 $\frac{3}{8}$ 60	Chrome
BV891213		Straight	$\frac{1}{2}$ " PEX x $\frac{3}{8}$ " OD Comp	1 $\frac{3}{16}$ 46	1 $\frac{1}{16}$ 18	2 $\frac{7}{8}$ 73	Chrome
BV890313		Straight	$\frac{1}{2}$ " IPS x $\frac{1}{2}$ " - $\frac{7}{16}$ " Rbr SJ	1 $\frac{3}{16}$ 46	1 $\frac{1}{4}$ 32	2 51	Chrome
BV892513		Straight	$\frac{1}{2}$ " Sweat w/5" Ext x $\frac{3}{8}$ " OD	1 $\frac{3}{16}$ 46	7 $\frac{5}{8}$ 194	2 $\frac{1}{4}$ 57	Chrome
BV889003		Angle	$\frac{3}{8}$ " IPS x $\frac{3}{8}$ " OD Comp	1 $\frac{3}{16}$ 46	$\frac{1}{16}$ 1	$\frac{7}{8}$ 23	Chrome
BV892503		Angle	$\frac{1}{2}$ " Comp with 5" Extension x $\frac{3}{8}$ " OD	1 $\frac{3}{16}$ 46	6 $\frac{13}{16}$ 173	2 $\frac{1}{4}$ 57	Chrome
BV892403		Angle	$\frac{1}{2}$ " CPVC x $\frac{3}{8}$ " OD Comp	1 $\frac{3}{16}$ 46	1 $\frac{7}{8}$ 48	$\frac{7}{8}$ 22	Chrome
BV8940LK		Angle	$\frac{5}{8}$ " OD x $\frac{3}{8}$ " OD loose key	1 $\frac{3}{16}$ 46	1 $\frac{5}{8}$ 41	1 $\frac{1}{8}$ 28	Chrome
BV890003		Angle	$\frac{1}{2}$ " IPS x $\frac{3}{8}$ " OD Comp	1 $\frac{3}{16}$ 46	1 $\frac{1}{2}$ 38	1 $\frac{1}{8}$ 28	Chrome
BV892003		Angle	$\frac{1}{2}$ " Copper Sweat x $\frac{3}{8}$ " OD Comp	1 $\frac{3}{16}$ 46	1 $\frac{13}{16}$ 46	1 $\frac{1}{8}$ 28	Chrome
BV894003		Angle	$\frac{5}{8}$ " OD Comp x $\frac{3}{8}$ " OD Comp	1 $\frac{3}{16}$ 46	1 $\frac{11}{16}$ 43	1 $\frac{1}{8}$ 28	Chrome
BV891203		Angle	$\frac{1}{2}$ " PEX x $\frac{3}{8}$ " OD Comp	1 $\frac{3}{16}$ 46	2 $\frac{1}{4}$ 57	$\frac{1}{2}$ 12	Chrome
BV894153		Angle	$\frac{5}{8}$ " OD Comp x $\frac{1}{4}$ " OD Comp	1 $\frac{3}{16}$ 46	1 $\frac{3}{4}$ 44	1 $\frac{1}{8}$ 28	Chrome
BV389003		3-Way	$\frac{1}{2}$ " IPS x $\frac{3}{8}$ " OD x $\frac{3}{8}$ " OD	1 $\frac{3}{16}$ 46	1 $\frac{7}{16}$ 37	1 $\frac{1}{8}$ 28	Chrome
BV389053		3-Way	$\frac{1}{2}$ " IPS x $\frac{3}{8}$ " OD x $\frac{1}{4}$ " OD	1 $\frac{3}{16}$ 46	1 $\frac{7}{16}$ 37	1 $\frac{1}{8}$ 28	Chrome
BV389403		3-Way	$\frac{5}{8}$ " OD x $\frac{3}{8}$ " OD x $\frac{3}{8}$ " OD	1 $\frac{3}{16}$ 46	1 $\frac{9}{16}$ 40	1 $\frac{1}{8}$ 28	Chrome

Pressure and Temperature

Maximum Pressure: 125psi (8.6 bar)

Maximum Temperature: 160°F (71.1°C)

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

USA: 815 Chestnut St., No. Andover, MA 01845-6098; www.watts.com

Canada: 5435 North Service Rd., Burlington, ONT. L7L 5H7; www.wattscanada.ca

ES-WB&T-KwikStop 0751

WATTS®

Brass & Tubular Products

© Watts Regulator Company, 2007