

For Commercial and Industrial Applications

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

Series FBV-3C, FBVS-3C

2-Piece, Full Port, Brass Ball Valves

Sizes: 1/4" – 4" (8 – 100mm)

Series FBV-3C 2-piece, full port, brass ball valves are used in commercial and industrial applications for a full range of liquids and gases. They feature a bottom-loaded blowout proof stem, virgin PTFE seats, thrust washer, and adjustable stem packing gland, stem packing nut, chrome plated brass ball, brass adapter, and steel handle.

Features

- CSA approved threaded valves only 1/4" – 3" (15 – 80mm)
- UL/FM approved threaded valves 1/2" – 2" (15 – 50mm)
- UL Listed solder valves 1/2" – 2" (15 – 50mm)
- Fluorocarbon elastomer stem O-ring prevents stem leaks
- Adjustable stem packing gland
- PTFE stem packing seal, thrust washer, and seats
- Bottom loaded blowout proof stem
- Machined chrome plated brass ball
- Valves comply to MSS-SP-110 standard
- Recommended for open/close applications

Models

FBV-3C: 1/4" – 4" (8 – 100mm) with threaded connections

FBVS-3C: 1/2" – 3" (15 – 80mm) with solder connections

Pressure – Temperature

Water Temperature Range: -40°F to 400°F (-40°C to 204°C)

Pressure Ratings

FBV-3C: 1/4" – 2" (8 – 50mm)

600psi (41 bar) WOG, non-shock
150psi (10.3 bar) WSP

2 1/2" – 4" (65 – 100mm)

400psi (27.5 bar) WOG, non-shock
125psi (8.6 bar) WSP

FBVS-3C: 1/2" – 2" (15 – 50mm)

600psi (41 bar) WOG, non-shock
150psi (10.3 bar) WSP

2 1/2" – 3" (65 – 80mm)

400psi (27.5 bar) WOG, non-shock
125psi (8.6 bar) WSP

*This valve is designed to be soft soldered into lines without disassembly, using a low temperature solder to 420°F (216°C). Higher temperature solders may damage the seat material.

NOTICE

Apply heat with the flame directed **AWAY** from the center of the valve body. Excessive heat can harm the seats. After soldering, the packing nut may have to be tightened.



Approvals

1/2" – 2" (15 – 50mm) FBV-3C UL/FM approved

1/2" – 2" (15 – 50mm) FBVS-3C UL Listed



Gas Approvals (Threaded Valves Only)

1/4" – 3/8" (8 – 10mm)

ASME B16.33, CSA
ASME B16.44



1/2 psig, 5psig, (14, 34 kPa) @ -40°F to 125°F (-40°C to 52°C)

1/2" – 2" (15 – 50mm) ASME B16.33, CSA
ASME B16.44



1/2 psig, 5psig, and 125psig (14, 34 and 862 kPa)
@ -40°F to 125°F (-40°C to 52°C)

2 1/2" – 3" (65 – 80mm)

ASME B16.38, CSA
ASME B16.44



1/2 psig, 5psig, and 125psig (14, 34 and 862 kPa)
@ -40°F to 125°F (-40°C to 52°C)

Specifications


Approved valves shall be 2-piece full port design constructed of a forged brass body and end adapter. Seats and stem packing shall be virgin PTFE. Stem shall be bottom loaded, blowout proof design with fluorocarbon elastomer O-ring to prevent stem leaks. Valve shall have chrome plated brass ball and adjustable packing gland. Threaded valves 1/2" – 3" (shall be CSA approved to 1/2, 5, and 125psig (14, 34 and 862 kPa), UL/FM approved. Solder valves to be UL listed. Valve sizes 1/4" – 2" (8 – 80mm) shall be rated to 600psi (41 bar) WOG non-shock and 150psi (10.3 bar) WSP. Valve sizes 2 1/2" – 4" (65 – 100mm) threaded, shall be rated to 400psi (27.5 bar) WOG non-shock and 125psi (8.6 bar) WSP. Valve sizes 2 1/2" – 3" (65 – 88mm) solder shall be rated to 400psi (27.5 bar) WOG non-shock and 125psi (8.6 bar) WSP. Valve shall be a Watts Series FBV-3C (threaded) or FBVS-3C (solder).

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.


Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

Materials




A. Handle Nut	Zinc plated carbon steel
B. Handle Assembly	Zinc plated carbon steel with vinyl insulator
C. Packing Nut	Brass
D. Stem Packing	Virgin PTFE
E. O-ring	Fluorocarbon elastomer (FKM)
F. Thrust Washer	Virgin PTFE
G. Stem	Machined Brass
H. Tag	Cardboard, Mylar coated both sides
I. Body	Forged Brass
J. Seats	Virgin PTFE
K. Ball	Chrome plated brass
L. Adapter	Forged Brass

Temperature – Pressure



*See applicable note on reverse side for solder end valves with regards to pressure/temperature rating.

Dimensions – Weights



SIZE (DN)		DIMENSIONS							WEIGHT						
in.	mm	C		H		H ₁		I		L		L ₁		lbs.	kg.
1/4	8	1 13/16	46	3 7/16	87	-	-	1/2	12.9	1 3/4	45	-	-	0.4	0.2
3/8	10	1 13/16	46	3 7/16	87	-	-	1/2	12.9	1 3/4	45	-	-	0.4	0.2
1/2	15	1 13/16	46	3 7/16	87	3 7/16	87	1/2	12.9	1 15/16	50	2 1/16	52	0.4	0.2
3/4	20	2 1/4	57	4	101	4	101	3/4	19.2	2 5/16	59	2 1/16	68	0.8	0.3
1	25	2 5/8	67	4 1/4	108	4 1/4	108	1	25.5	2 13/16	72	3 1/4	83	1.2	0.5
1 1/4	32	2 13/16	71	4 1/4	108	4 1/4	108	1 1/4	31.9	3 3/16	81	3 1/16	94	1.8	0.8
1 1/2	40	3 3/16	80	5 1/4	134	5 5/16	135	1 1/4	38.0	3 1/2	88	4 1/4	108	2.6	1.2
2	50	3 1/2	89	6	153	6	153	2	50.9	4 1/8	105	5 5/16	135	3.7	1.7
2 1/2	65	4 1/16	104	7 3/8	187	7 3/8	188	2 1/2	63.6	5 5/16	134	6 1/4	158	7.1	3.2
3	80	4 1/2	114	7 3/4	197	7 3/4	197	3	76.3	6 1/16	154	7 3/8	185	11.3	4.7
4	100	5 3/8	136	9 5/8	245	-	-	4	101.6	7 7/16	189	-	-	17.7	8.0



A Watts Water Technologies Company



ISO 9001-2008
CERTIFIED

USA: Tel: (978) 688-1811 • Fax: (978) 794-1848 • www.watts.com
Canada: Tel: (905) 332-4090 • Fax: (905) 332-7068 • www.watts.ca