For Residential and Commercial Applications				
Job Name		Engineer / Architect		
Job Location		Wholesaler		
Submittal Date		Contractor		

1-**KC/ 3-**KC Copper Faucet Riser – Compression Nosepiece

Use: For use in potable water distribution systems in accessible locations only.

Design Features:

- One-piece construction
- Cut-to-Length for clean, professional installation
- 100% Compliant to California and Vermont "low-lead" requirements





Temperature: 40°- 180° F

Pressure: 125 psi maximum

Tubing Diameter: 0.38" O.D. or 0.50" O.D.




MATERIAL SPECIFICATIONS				
Tube C12200 copper per ASTM B-68				
Compression Nut	C36000 brass			
Compression Sleeve	C36000 brass			

Part Listing:

1-12KC C	3/8" Compression x 3/8" OD Tube x 11-1/2" Length, chrome plated
1-12KC CBT	3/8" Compression x 3/8" OD Tube x 11-1/2" Length, chrome plated, bulk
1-12KC C2	3/8" Compression x 3/8" OD Tube x 11-1/2" Length, chrome plated, 2 per pack
1-12KC R	3/8" Compression x 3/8" OD Tube x 11-1/2" Length, rough finish
1-12KC RBT	3/8" Compression x 3/8" OD Tube x 11-1/2" Length, rough finish, bulk
1-12KC R2	3/8" Compression x 3/8" OD Tube x 11-1/2" Length, rough finish, 2 per pack
1-15KC C	3/8" Compression x 3/8" OD Tube x 14-1/2" Length, chrome plated
1-15KC R	3/8" Compression x 3/8" OD Tube x 14-1/2" Length, rough finish
1-20KC C	3/8" Compression x 3/8" OD Tube x 19-1/2" Length, chrome plated
1-20KC CBT	3/8" Compression x 3/8" OD Tube x 19-1/2" Length, chrome plated, bulk
1-20KC CF	3/8" Compression x 3/8" OD Tube x 19-1/2" Length, chrome plated, flag label
1-20KC C2	3/8" Compression x 3/8" OD Tube x 19-1/2" Length, chrome plated, 2 per pack
1-20KC R	3/8" Compression x 3/8" OD Tube x 19-1/2" Length, rough finish
1-20KC R2	3/8" Compression x 3/8" OD Tube x 19-1/2" Length, rough finish, 2 per pack
1-30KC C	3/8" Compression x 3/8" OD Tube x 29-1/2" Length, chrome plated
3-12KC C	1/2" Compression x 1/2" OD Tube x 11-1/2" Length, chrome plated

1-**KC/ 3-**KC Copper Faucet Riser – Compression Nosepiece



PART DIMENSIONS (Inches)					
Model	DIM. A	DIA. B			
1-12KC	11.56	3/8			
1-15KC	14.56	3/8			
1-20KC	19.56	3/8			
1-30KC	29.56	3/8			
3-12KC	12.56	1/2			

Listings & Certifications:

- IAPMO listed to ASME A112.18.1–2005 / CSA B125.1-2005 (File # 0645)
- CSA approved to California Health & Safety Code 116875 and Vermont Bill S.152 (Project # 2174785)

