

Liberty Pumps®

Model 101

Cast Iron Pedestal Sump Pump

1/3 hp

1-1/4" Discharge

Features:

- 1/3 hp Motor with automatic thermal overload protection, 8 ft 3-wire power cord, and ground plug.
- Adjustable level control for most efficient pumping operation.
 - Double inlet screening to prevent clogging.
- High-strength cast impeller for impact and abrasion resistance.
- Extra large base for added stability.
 - Exclusive shaft seal to isolate bearing from impeller cavity.
- Flexible shaft coupling for quiet, vibration-free performance.



innovate. evolve.

Model 101 Cast Iron

Pedestal Sump Pump

Motor:

1/3 hp, continuous-duty, 1725 rpm, PSC.

Switch:

Specially designed dual-contact, top-mounted, float and rod activated.

Housing:

Durable heavy duty cast iron, enamel coated.

Column:

Corrosion-resistant zinc-coated steel.

Bearing:

Oil impregnated bronze with oil retaining felt reservoir.

Impeller:

Cast iron, large, open non-clog design.

Discharge:

1-1/4" FPT.

High - Temp Pedestal Pump

Model 101H: Cast Iron

For use in water up to 200° F. The H-option incorporates a stainless steel impeller shaft, copper float and metal rod guide.

Performance:

Capacity	TDH	5'	10'	15'	18' MAX HEAD
	GPH	3150	2380	1260	0

All models are tested and rated in accordance with SSPMA standards.



Dual Safety certification for the United States and Canada.

Specifications subject to change without notice.