



TechData

PRODUCT SPECIFICATION SHEET



ProRadiant
SYSTEMS

3-Speed Circulator Pumps (Low, High Head)

Applications

Viega offers two 3-speed, wet rotor, direct drive in-line circulator pumps designed for residential and light commercial applications. These circulators are quiet and maintenance free, making them ideal to use in primary and / or secondary loop piping.



Specifications

LOW HEAD

Flow range: 0 - 17.5 US GPM
Head range: 0 - 19 feet
Motor: 2 pole, single phase
Maximum fluid temperature: 230°F
Minimum fluid temperature: 36°F
Maximum working pressure: 145 PSI
Maximum glycol mix: 50%

HIGH HEAD

Flow range: 0 - 34 US GPM
Head range: 0 - 30 feet
Motor: 2 pole, single phase
Maximum fluid temperature: 230°F
Minimum fluid temperature: 36°F
Maximum working pressure: 145 PSI
Maximum glycol mix: 50%



Stock Code	A	B	C	D	E	F
Low Head 12126	6 1/2"	5 1/4"	4"	4 3/16"	3"	3 5/32"
High Head 12127	6 1/2"	6"	4 7/8"	3 7/8"	3 7/16"	3 5/32"



VIEGA
301 N. Main, 9th Floor
Wichita, KS 67202
Phone: 1-877-843-4262
Fax: 1-800-976-9817

service@viega.com
www.viega.com




TechData

PRODUCT SPECIFICATION SHEET




ProRadiant
SYSTEMS

Stock Code	Speed	Amps	Watts	HP
12126	HI	0.75	87	1/25
	MED	0.66	80	1/25
	LOW	0.55	60	1/25



Stock Code	Speed	Amps	Watts	HP
12127	HI	1.8	197	1/6
	MED	1.5	179	1/6
	LOW	1.3	150	1/6



VIEGA
301 N. Main, 9th Floor
Wichita, KS 67202
Phone: 1-877-843-4262
Fax: 1-800-976-9817

service@viega.com
www.viega.com