

## Thread and Gasket Sealant



### DESCRIPTION

All purpose, high performance pipe joint and gasket sealing compound for use on metals including Aluminum, Black Iron, Brass, Copper, Stainless Steel, Galvanized Steel and on Plastics including PVC and CPVC. **Block** sets up quickly and dries to form a very tough, yet flexible seal which will not harden, crack, crumble or shrink. Provides leak-proof resistance to high pressure, temperature, expansion, contraction and extreme vibration. Joints can be disassembled easily, without damage to pipe or equipment. **Block** can be removed from skin or clothing, tools or equipment with isopropyl alcohol.

Ideal for sealing jobs in plumbing, heating, piping, air conditioning, refrigeration, automotive and innumerable industrial applications. **Block** is applied easily with the natural bristle brush even at temperatures as low as +20°F and performs over a temperature range of -90°F to +450°F. It provides leak proof hydraulic resistance to 12,000 psi and withstands gas pressure to 2,600 psi. **Block** contains no lead.

### SIZES AND PACKING

STOCK NO.	SIZE	PACKING	WEIGHT/CASE
15-703	1/4 pt.*	24	13.0 lbs.
15-707	1/2 pt.*	24	20.8 lbs.
15-711	1 pt.*	12	21.0 lbs.
15-716	1 qt.*	12	39.0 lbs.

\*brush-in-cap



specifications

Block™

