

Model 860 & 860FT

Resilient Seated Ball Type Test Cocks

Application

Designed for installation on backflow preventers as a test port for attaching a differential pressure gauge. Optional SAE flare fitting allows for fast and easy attachment of test kit hoses. A threaded dust cover is included with the 860FT to protect against fouling caused by insects, dirt and debris.

Materials

Main valve body Cast Bronze ASTM B 584

Brass ASTM B 16, Chrome Plated Ball

Seat & packing Teflon

Flare fitting Brass ASTM B 16

Features

Sizes: 1/8", 1/4"


300 PSI WOG Maximum pressure 180°F Maximum temperature End connections Threaded ANSI B1.20.1 Flare connection (860FT) 45° Flare SAE





Model 860



Typical Installation







MODEL 860FT

INDOOR INSTALLATION (350)

Dimensions & Weights (do not include pkg.)

billiensions & weights (do not include pkg.)										
	MODEL	SIZE	DIMENSIONS (approximate)						WEIGHT	
			Α		В		С		VVEIGHT	
			in	mm	in.	mm	in.	mm	lbs.	kg
	18-860	1/8" MNPT X 1/4" FNPT	1 5/8	41	3/4	19	3/8	10	1	0.5
	14-860	1/4" MNPT X 1/4" FNPT	1 5/8	41	3/4	19	3/8	10	1	0.5
	18-860FT	1/8" MNPT X 45° SAE	2	51	3/4	19	3/8	10	1	0.5
	14-860FT	1/4" MNPT X 45° SAE	2	51	3/4	19	3/8	10	1	0.5

Zurn Industries, LLC | Wilkins

1747 Commerce Way, Paso Robles, CA U.S.A. 93446 Ph. 855-663-9876, Fax 805-238-5766

In Canada | Zurn Industries Limited

3544 Nashua Drive, Mississauga, Ontario L4V 1L2 Ph. 905-405-8272, Fax 905-405-1292

Rev. A Date: 5/13 Document No. BV-860 Product No. Model 860 & 860FT