

THIS SPACE FOR DESIGNER/ENGINEER APPROVAL

Job/Customer _____	Date _____	Contractor _____
Model Specified _____	Qty _____	Approved By _____
Designer/Engineer _____	Date _____	Contractor's PO# _____
Submitted by _____	Date _____	Other _____

4170 Series



Full Port Forged Brass Ball Valves

IPS

600 WOG / 150 WSP (400 WOG for 2 1/2" - 4")

ISO 9001

ITEM #	SIZE	CTN	CASE	A	B	C	D	Cv
w/ CHROME PLATED LEVER HANDLE								
41700	1/4	10	120	1/4	1 3/4	1 7/8	3 1/2	7.7
41701	3/8	10	120	3/8	1 3/4	1 7/8	3 1/2	7.9
41702	1/2	10	100	1/2	2 1/16	2 1/16	3 1/2	11.5
41703	3/4	10	60	3/4	2 5/8	2 5/8	3 3/4	27.0
41704	1	6	48	1	2 3/4	2 3/4	4 5/8	49.3
41705	1 1/4	4	32	1 1/4	3 5/16	3	4 1/2	114.0
41706	1 1/2	2	24	1 1/2	3 11/16	3 5/8	5 1/2	161.3
41707	2	2	16	2	4 3/16	4	5 1/2	248.6
41708	2 1/2	2	6	2 1/2	5 5/16	4 7/8	9	262.3
41709	3	1	3	3	6	5 1/2	9	418.2
41710	4	1	2	4	7 1/8	6	9 3/4	567.8
w/ 304 STAINLESS STEEL HANDLE								
41702SSL	1/2	10	100	1/2	2 1/16	2 1/16	3 1/2	11.5
41703SSL	3/4	10	60	3/4	2 5/8	2 5/8	3 3/4	27.0
41704SSL	1	6	48	1	2 3/4	2 3/4	4 5/8	49.3
41705SSL	1 1/4	4	32	1 1/4	3 5/16	3	4 1/2	114.0
41706SSL	1 1/2	2	24	1 1/2	3 11/16	3 5/8	5 1/2	161.3
41707SSL	2	2	16	2	4 3/16	4	5 1/2	248.6
w/ WING STYLE "T" HANDLE*								
41702T	1/2	10	100	1/2	2 1/16	2 1/16	1 3/4	11.5
41703T	3/4	10	60	3/4	2 5/8	2 5/8	1 3/4	27.0
41704T	1	6	48	1	2 3/4	2 3/4	1 3/4	49.3
w/ 304 STAINLESS STEEL WING STYLE "T" HANDLE								
41702SSW	1/2	10	100	1/2	2 1/16	2 1/16	1 3/4	11.5
41703SSW	3/4	10	60	3/4	2 5/8	2 5/8	1 3/4	27.5
41704SSW	1	6	48	1	2 3/4	2 3/4	1 3/4	49.3



NO.	DESCRIPTION	MATERIAL
1	BODY	BRASS
2	END CAP	BRASS
3	SEAT	PTFE
4	BALL	BRASS HCP
5	STEM	BRASS
6	STEM SEAL	PTFE
7	PACKING GLAND	BRASS
8	LEVER HANDLE	STEEL CP (FOR 4170) STAINLESS STEEL (FOR 4170SSL)
9	HANDLE NUT	STEEL CP (FOR 4170) STAINLESS STEEL (FOR 4170SSL)
10	HANDLE JACKET	VINYL
11	WING STYLE "T" HANDLE	STAINLESS STEEL (FOR 4170SSW) STEEL CP (FOR 4170T)
12	HANDLE NUT	STAINLESS STEEL (FOR 4170SSW) STEEL CP (FOR 4170T)

TEMP °F	1/4" - 2" PSI	2 1/2" - 4" PSI
100	600	400
150	490	327
200	479	313
250	470	293
300	411	274
350	294	196
366	N/A	N/A

Specifications: Designed for residential, commercial or industrial use with water, oil or gas. This approved Webstone valve is actuated by a blowout proof stem and features an adjustable packing gland. Threaded ends comply with ANSI B1.20.1. *4170T valves are not manufactured in an ISO facility. UPC certification applies to valves 1/2" to 2", and is not applicable to the 4170SSW series.

Webstone
VALVE INNOVATION

Quality and Commitment Since 1954

www.webstonevalves.com P: (800) 225-9529 · F: (800) 336-5133

Webstone product specifications in U.S. customary units are approximate and are provided for reference only. Webstone reserves the right to change or modify product design, construction, specifications or materials without prior notice and without incurring any obligation to make such changes and modifications on Webstone products previously or subsequently sold.

4170spec_082511