

Gas Furnace MODEL 340AAV Multi-Poise



Worry-Free, Money-Saving Heating.

A History of Making America Comfortable

Bryant has been making American homeowners comfortable since 1904. Through the commitment and dedication of our product development and manufacturing teams, we have consistently met every new challenge head-on and delivered the products to meet or exceed expectations. Today, as concerned consumers consider both initial price and monthly heating costs, Bryant offers our most affordable 90% AFUE gas furnace - the Model 340AAV.

The Bryant Model 340AAV provides reliable heating from a name you can trust. It offers peace of mind with limited lifetime warranty coverage on the heat exchangers. And, it saves on monthly heating costs with extra energy efficiency of up to 92% AFUE. Designed, built and backed by the most trusted name in the business, and installed by your trusted and professional Bryant dealer, the Model 340AAV provides the comfort and efficiency you and your family deserve.

Warranty

To the original owner, the Bryant model 340AAV gas furnace is covered by a 5-year parts limited warranty. Primary heat exchanger carries a 20-year parts limited warranty. Secondary heat exchangers also carry a 20-year labor limited warranty. See warranty certificate at bryant.com for complete details. Ask your Bryant dealer about optional extended warranties, which may include labor.

Extra Performance, Quiet Comfort

Standard furnaces rely on one heat exchanger to achieve industry minimum efficiency. Bryant's patented secondary heat exchanger helps the Model 340AAV transfer an additional 11 - 15% of the available heat into your home for money savings, energy efficiency and comfort. For quiet operation, a sealed combustion system, redesigned door and vibration-absorbing grommets and cabinet seals keep noise to a minimum, while highlighting the craftsmanship you get when you choose Bryant.

In addition, Bryant's Model 340AAV delivers the peace of mind that comes with choosing a system backed by a company committed to customer satisfaction. From initial design through product testing and an assembly process that includes thorough reliability testing procedures, we go beyond the industry's expectations for quality to be sure that every unit we make measures up to even tougher standards - yours.

Performance








As an ENERGY STAR® Partner, Bryant Heating & Cooling Systems has determined that this product meets the ENERGY STAR® quidelines for energy efficiency.

Home Comfort Components



EXTRA GAS EFFICIENCY

Our secondary heat exchanger extends heat transfer for higher efficiency use of heating fuel. It is protected by our patented Everlastic[™] coating for lasting corrosion resistance and durability.

RELIABILITY

Bryant's Perfect Light™ igniter is one of the most reliable and robust hot surface igniters available, so you can count on heating when you need it.

RESPONSIVE OPERATION

This reliable control responsively activates system operation for peak performance and energy efficiency.

QUIET, DRAFT-FREE COMFORT Our sealed combustion system virtually eliminates drafts and allows quiet operation by using outdoor air for combustion.

Model 340AAV

This Box is to be used as a knock-out for a non-varnished area on a full-spread. full-bleed varnish plate.

bryant **Heating & Cooling Systems**

A Member of the United Technologies Corporation Family. Stock Symbol UTX.

01-8340-300-50

© Bryant Heating and Cooling Systems 2009 7310 West Morris Street, Indianapolis, IN 46231

Visit our website at www.bryant.com

Printed on recycled paper.

