

Air Bear® Cub

Media Whole-House Air Cleaners



TECHNICAL SPECIFICATION



Performance:


- Rated airflow up to 1200 CFM.
- Non-woven, 3" thick, pleated Air Bear® media filter traps particles as small as 1 micron.
- Tested using ANSI/ASHRAE 52.2 - 2007 standard procedures.
- Efficiency rating of MERV 8 or MERV 11.

Features:

- Quick and easy installation.
- Air Bear® filters capture and hold pollutants inside the filter, allowing air to flow freely through the system.
- Highly-efficient, 100% electrostatically-charged synthetic material features extended surface pleats that have higher dirt-holding capacity than competitive filters.
- Narrow Profile: Fits in tight spaces.
- Mounts directly to heating and cooling systems.
- Suitable for use with all types of central forced-air configurations.
- Rugged cabinet construction for long life.



*Another True Member of
The Air Bear® Family*




Warranty:

- 10-Year limited warranty on cabinet.

TECHNICAL SPECIFICATION

Air Bear® Cub Dimensions



Model	Air Bear® Cub	
Part No.	259859-001	259859-002
Rated Airflow	1200 CFM	1200 CFM
MERV Rating	8	11
Media Size (Inches)	3" D x 15 3/4" H x 24 1/4" W	3" D x 15 3/4" H x 24 1/4" W
Optional Accessories	Pre-Filter	Pre-Filter
	Charcoal After-Filter	Charcoal After-Filter
Media Part No. (6 Pack)	255649-101	259112-101
Media Type	100% Synthetic Disposable / Factory Assembled	100% Synthetic Disposable / Factory Assembled
Media Listing	UL Classified (See complete marking on product.)	UL Classified (See complete marking on product.)
Cabinet Finish	Powder-Coated Paint Finish	Powder-Coated Paint Finish
Shipping Weight	12 lbs	12 lbs
Universal Application	Right / Left-Hand Installation	Right / Left-Hand Installation

Air Bear® Air Cleaners have been tested using ANSI / ASHRAE 52.2-2007 standard test procedures.


Indoor Air Quality Since 1948.

ISO 9001:2008 Certified.

Industry Memberships:



Proudly Designed,
Engineered, and
Manufactured in
North Carolina.



To help serve you better,
please contact us at:

800-884-0002 (tel)

800-458-2379 (fax)

Trion®

101 McNeill Road
Sanford, NC 27330

www.trioniaq.com

customerservice@trioniaq.com

Trion® is a registered trademark of Air System Components, Inc. All product specifications reflect available information at the printing of this brochure. Trion® reserves the right to revise or modify products and/or specifications without notice. ©2012 Trion®.