







| Position | Count | Description | Unit price |
|----------|-------|---|------------|
| | -1 | <p>UPS 26-99 FC</p>  <p>Product photo could vary from the actual product</p> <p>Product No.: 52722513 The pump is of the canned rotor type, i.e. pump and motor form an integral unit without shaft seal and with only two gaskets for sealing. The bearings are lubricated by the pumped liquid. The pump is characterized by:</p> <ul style="list-style-type: none"> * Ceramic shaft and radial bearings. * Carbon axial bearing. * Stainless steel rotor can and bearing plate. * Corrosion-resistant impeller, Composite, PES. * Cast iron pump housing. <p>The motor is a 1-phase motor. No additional motor protection is required.</p> <p>Liquid: Liquid temperature range: 35.6 .. 230 °F Density: 62.4 lb/ft³</p> <p>Technical: Maximum operating pressure: 145 psi Approvals on nameplate: UL, CSA</p> <p>Materials: Pump housing: Cast iron EN-JL1030 ASTM 30 B Impeller: Composite, PES</p> <p>Installation: Maximum ambient temperature: 104 °F Ambient max at 176°F liquid: 176 °F Maximum operating pressure: 145 psi Flange standard: USA Oval Type of connection: C.I. Flange Pipe connection: 2 - Bolt Flange Pressure stage: 10 Port-to-port length: 6 1/2 in</p> | On request |

| Position | Count | Description | Unit price |
|----------|-------|---|------------|
| | | <p>Electrical data:</p> <p>Number of poles: 2</p> <p>Power input in speed 1: 150 W</p> <p>Power input in speed 2: 179 W</p> <p>Max. power input: 196 W</p> <p>Rated power - P2: 0.161 HP</p> <p>Main frequency: 60 Hz</p> <p>Rated voltage: 1 x 230 V</p> <p>Current in speed 1: 0.7 A</p> <p>Current in speed 2: 0.8 A</p> <p>Current in speed 3: 0.9 A</p> <p>Capacitor size - run: 5 µF/400 V</p> <p>Insulation class (IEC 85): F</p> <p>Others:</p> <p>Gross weight: 10.3 lb</p> | |

| Description | Value |
|------------------------------|--|
| Product name: | UPS 26-99 FC |
| Product Number: | 52722513 |
| EAN number: | 5700834818714 |
| Technical: | |
| Speed Number: | 3 |
| Max flow: | 33 US gpm |
| Head max: | 28.9 ft |
| Maximum operating pressure: | 145 psi |
| Approvals on nameplate: | UL, CSA |
| Valve: | pump with built-in isolating and non-return valves |
| Materials: | |
| Pump housing: | Cast iron |
| | EN-JL1030 |
| | ASTM 30 B |
| Impeller: | Composite, PES |
| Installation: | |
| Maximum ambient temperature: | 104 °F |
| Ambient max at 176°F liquid: | 176 °F |
| Maximum operating pressure: | 145 psi |
| Flange standard: | USA Oval |
| Type of connection: | C.I. Flange |
| Pipe connection: | 2 - Bolt Flange |
| Pressure stage: | 10 |
| Port-to-port length: | 6 1/2 in |
| Liquid: | |
| Liquid temperature range: | 35.6 .. 230 °F |
| Density: | 62.4 lb/ft³ |
| Electrical data: | |
| Number of poles: | 2 |
| Power input in speed 1: | 150 W |
| Power input in speed 2: | 179 W |
| Max. power input: | 196 W |
| Rated power - P2: | 0.161 HP |
| Main frequency: | 60 Hz |
| Rated voltage: | 1 x 230 V |
| Current in speed 1: | 0.7 A |
| Current in speed 2: | 0.8 A |
| Current in speed 3: | 0.9 A |
| Capacitor size - run: | 5 µF/400 V |
| Insulation class (IEC 85): | F |
| Motor protection: | CONTACT |
| Thermal protec: | internal |
| Controls: | |
| Pos term box: | 9H |
| Others: | |
| Gross weight: | 10.3 lb |



52722513 UPS 26-99 FC 60 Hz



Note! All units are in [mm] unless others are stated.
Disclaimer: This simplified dimensional drawing does not show all details.