

Job Name : _____
Purchaser : _____
Engineer : _____
Submitted To : _____
Submitted By : _____
Unit Designation : Schedule No.: _____

Location : _____
P.O. No. : _____
Architect : _____
Date : _____
For : ☐ Reference ☐ Approval ☐ Construction
Model No.: _____

Submittal Data : LS092CE

Air Conditioner Single Zone Mini Split



Capacities :

Rated Cooling Capacity (Btu/h)	9,000
Power Input (W)	780
SEER	13.0
EER	11.5

Cooling Nominal Test Condition :

Indoor : 80 DB / 67 WB
Outdoor : 95 DB / 75 WB
Pipe Length : 25ft

Indoor Unit :

Power Supply (V,Ph,HZ)	36V DC
Minimum Circuit Ampacity (A)	Powered by outdoor unit
Maximum Overcurrent Protection (A)	Powered by outdoor unit
Weight (lbs)	15.4
Sound Pressure (dB(A), H/M/L Cool, 3.3ft front)	36/31/28
Air Circulation (CFM, H/M/L Cool)	250/210/170
Dehumidification (pts/hr)	2.6
Drain Pipe (inches, O.D, I.D)	3/4, 5/8

Outdoor Unit :

Power Supply (V,Ph,HZ)	115,1,60
Minimum Circuit Ampacity (A)	15
Maximum Overcurrent Protection (A)	15
Running Current (A)	7.0
Weight (lbs)	66.1
Sound Pressure (dB(A), High Cool, 3.3ft front)	48

Refrigerant Piping :

Maximum Length (ft)	50
Maximum Height Difference (ft)	25
Liquid Side (inches, O.D)	1/4
Gas Side (inches, O.D)	3/8
Refrigerant	R410A

Operating Range :


Cooling Operating Range (, standard)	0 - 115
---------------------------------------	---------

Standard Features :

- Five Year Compressor Warranty
- Two Year Functional Parts Warranty
- Plasma Air Purifying System
- Chaos Swing Air Circulation
- Jet Cool ™
- LCD Wireless Remote Controller
- Auto Restart
- 24 Hour On/Off Timer
- Built-in Low Ambient Standard down to 0 at cooling mode

Note :

LSN092CE



LSU092CE

