



Position	Count	Description	Unit price
	-1	UP 15-18 B5  Product photo could vary from the actual product Product No.: 59896118 The pump is of the canned rotor type, i.e. pump and motor form an integral unit without shaft seal and with only two gaskets for sealing. The bearings are lubricated by the pumped liquid. The pump is characterized by: * Ceramic shaft and radial bearings. * Carbon axial bearing. * Stainless steel rotor can and bearing plate. * Corrosion-resistant impeller, Composite, PES. * Bronze pump housing. The motor is a 1-phase motor. No additional motor protection is required. Liquid: Liquid temperature range: 35.6 .. 230 °F Density: 62.4 lb/ft³ Technical: Maximum operating pressure: 145 psi Approvals on nameplate: UL, CSA Materials: Pump housing: Bronze DIN W.-Nr. 2.1176.01 Impeller: Composite, PES Installation: Maximum ambient temperature: 104 °F Ambient max at 176°F liquid: 176 °F Maximum operating pressure: 145 psi Flange standard: USA Sweat Type of connection: Bronze Sweat Pipe connection: 1/2" Sweat Pressure stage: 10 Port-to-port length: 5 in Electrical data:	On request


Position	Count	Description	Unit price
		Number of poles: 2 Max. power input: 90 W Rated power - P2: 0.04 HP Main frequency: 60 Hz Rated voltage: 1 x 230 V Current in speed 3: 0.4 A Capacitor size - run: 2 µF/400 V Insulation class (IEC 85): F Others: Gross weight: 6 lb	

Company name: -
 Created by: -
 Phone: -
 Fax: -
 Date: -

Description	Value
Product name:	UP 15-18 B5
Product Number:	59896118
EAN number:	5700391411397
Technical:	
Speed Number:	1
Max flow:	14.5 US gpm
Head max:	13.8 ft
Maximum operating pressure	145 psi
Approvals on nameplate:	UL, CSA
Materials:	
Pump housing:	Bronze
	DIN W.-Nr. 2.1176.01
Impeller:	Composite, PES
Installation:	
Maximum ambient temperature:	104 °F
Ambient max at 176°F liquid	176 °F
Maximum operating pressure	145 psi
Flange standard:	USA Sweat
Type of connection:	Bronze Sweat
Pipe connection:	1/2" Sweat
Pressure stage:	10
Port-to-port length:	5 in
Liquid:	
Liquid temperature range	35.6 ... 230 °F
Density:	62.4 lb/ft³
Electrical data:	
Number of poles:	2
Max. power input:	90 W
Rated power - P2:	0.04 HP
Main frequency:	60 Hz
Rated voltage:	1 x 230 V
Current in speed 3	0.4 A
Capacitor size - run	2 µF/400 V
Insulation class (IEC 85):	F
Motor protection:	CONTACT
Thermal protec:	internal
Controls:	
Pos term box:	9H
Others:	
Gross weight:	6 lb



59896118 UP 15-18 B5 60 Hz



Note! All units are in [mm] unless others are stated.
Disclaimer: This simplified dimensional drawing does not show all details.