



TechData

PRODUCT SPECIFICATION SHEET



PureFlow® Bronze PEX Press Fittings and Stainless Steel Press Sleeves for ViegaPEX™, ViegaPEX™ Ultra, ViegaPEX™ Barrier and FostaPEX™ SDR-9 Cross-linked Polyethylene (PEX)

Scope

This product specification designates the requirements for PureFlow Bronze PEX Press fittings and stainless steel press sleeves to be used as connections for ViegaPEX, ViegaPEX Ultra, ViegaPEX Barrier, and FostaPEX tubing in 3/8", 1/2", 5/8", 3/4", 1", 1-1/4", and 1-1/2" sizes as available. The connections are to be completed with the aid of a PureFlow PEX Press Hand Tool or PureFlow PEX Press Power Tool.

Materials

PureFlow Bronze PEX Press fittings are cast and machined from a solid Bronze alloy. This gives the fitting high corrosion and stress crack resistance. All PureFlow PEX Press fittings are precision made to tight tolerances for a consistent fit with ViegaPEX tubing. All PureFlow PEX Press fittings meet the rigorous requirements of ANSI/NSF-61 for lead extraction.

The stainless steel press sleeves are manufactured from 304 stainless steel that will not corrode, maintaining a clean appearance for the lifetime of the system.

Marking and Certification

PureFlow Bronze PEX Press fittings and stainless steel sleeves are manufactured and certified to the requirements of ASTM F877. PureFlow PEX Press fittings and sleeves are marked with the size, manufacturers mark, and required marking(s) of third party certification organizations. Fittings also meet the requirements of ANSI/NSF-61 for health effects and are suitable for contact with potable water. NSF International and other certification organizations conduct random on-site inspections of manufacturing facilities and independently test PureFlow Bronze PEX Press fittings for compliance with physical, performance, and toxicological standards.

Recommended Uses

PureFlow Bronze PEX Press fittings and stainless steel press sleeves are intended and recommended for use in potable water distribution systems with ViegaPEX, ViegaPEX Ultra, and FostaPEX tubing, and for hydronic heating, snow melt, and cooling systems with ViegaPEX Barrier and FostaPEX tubing meeting the requirements of ASTM F876. Maximum design temperature and pressure ratings are 160 psi @ 73°F, 100 psi @ 180°F and 80 psi @ 200°F. PureFlow Bronze PEX Press fitting system components are only available from Viega and are not interchangeable with components and tubing from other suppliers. For information on other hot and cold applications not listed here, consult with your Viega representative.

Handling and Installation

PureFlow Bronze PEX Press fittings are cast and machined from a solid bronze alloy and precision made to tight tolerances. Use of these materials in hot and cold water distribution systems must be in accordance with good plumbing practices, applicable code requirements, and current installation practices available from Viega. Contact a Viega representative or the applicable code enforcement bureau for information about approvals for specific applications.





TechData

PRODUCT SPECIFICATION SHEET



PureFlow® Bronze PEX Press Fittings and Stainless Steel Press Sleeves for ViegaPEX™, ViegaPEX™ Ultra, ViegaPEX™ Barrier and FostaPEX™

Quality Assurance

When the product is marked with the ASTM F877 designation, it affirms that the product was manufactured, inspected, sampled and tested in accordance with these specifications and has been found to meet the specified requirements.

Certifications

NSF-pw - NSF International Performance and Health Effects (Standards 14 & 61)


UPC - IAPMO Certified

NSF - NSF certified to CSA B137.5 (Canadian Standards Association)

PureFlow Bronze PEX Press Fittings Typical Fitting Insert Dimensions

SIZE	A	B	L
3/8"	.232	0.355±.003	0.583
1/2"	.354	0.475±.003	0.583
5/8"	.449	0.573±.003	0.583
3/4"	.543	0.668±.003	0.583
1"	.724	0.862±.004	0.740
1-1/4"	.862	1.049±.004	0.933
1-1/2"	1.059	1.238±.004	0.933

NOTE: Dimensions are in English units. Tolerances shown are Viega requirements. Viega Bronze PEX Press fittings are manufactured within these specifications.




(number of ribs may vary per fitting size)

Friction Loss Table For PureFlow Bronze PEX Press Fittings Expressed in Equivalent Length of Tubing in Feet

SIZE	COUPLING	90° ELBOW	TEE RUN	TEE BRANCH
3/8"	2.9	9.2	2.9	9.4
1/2"	2.0	9.4	2.2	10.4
3/4"	0.6	9.4	1.9	8.9
1"	1.3	10.0	2.3	11.0
1-1/4"	5.5	11.0	4.8	13.0
1-1/2"	6.1	13.0	5.0	16.0

This information is based on tubing nominal flow rate. (@ 8 fps flow velocity)

Stainless Press Sleeve



Pressed Sleeve

A pressed fitting has jaw witness marks indicating the connection has been properly made.

