

End Cap with Vent, R32

Submittal Information

Revision A: Feb. 20, 2009

Project Information

Job Name:

Location:

Part No. Ordered:

Engineer:

Date Submitted:

Contractor:

Submitted By:

Manufacturer's Representative:

Approved By:

Technical Data

Material:	UNS C3850 Brass
Maximum Working Pressure:	145 psi
Maximum Temperature/Flow:	220°F (104°C)/21.0 gpm
Connection:	1¼" BSP

Product Information and Application Use

The End Cap with Vent, R32, caps the end of the TruFLOW™ Jr. Modular Manifolds. It comes complete with swivel drain valve and manual air vent. Required gasket (A2403232) is included.



✓	Description	Part Number	Length	Width	Height	Weight
	The End Cap with Vent, R32	A2803250	2.75"	1.75"	3.500"	.900 lbs.
	Manifold Gasket, spare part	A2403232	1.56"	1.56"	0.625"	.005 lbs.

Installation

Use with TruFLOW Jr. Manifolds (not preassembled). Use these end caps for the top manifold, following procedures outlined in the Uponor Radiant Installation Handbook.

Standards

N/A

Codes

N/A

Listings

N/A

Related Applications

Radiant Heating and Cooling Systems

Contact Information

Uponor, Inc.
5925 148th Street West
Apple Valley, MN 55124 USA
Phone: (800) 321-4739
Fax: (952) 891-2008
www.uponor-usa.com

Uponor Ltd.
2000 Argentia Rd., Plaza 1, Ste. 200
Mississauga, ON L5N 1W1 CANADA
Phone: (888) 994-7726
Fax: (800) 638-9517
www.uponor.ca