

Field Calibration of Series AFS Sensing Switches Bulletin AFS-04.00

To adjust the set point on any Cleveland Controls Series AFS Air Switch with Adjustment Range of 0.05 - 12.0"w.c. ± 0.02 " w.c.:

Turn the adjusting screw counter-clockwise until motion has stopped. Next, turn the adjusting screw four complete turns in a clockwise direction to engage the spring. From this point, the next **ten turns** will be used for the actual calibration: **Each full turn represents approximately 1.2" w.c..** *example*:

To set the switch at 3.0" w.c., turn the screw counter-clockwise until travel stops. Then turn four turns in a clockwise direction to engage the spring. A further 2 1/2 turns in a clockwise direction will result in a setting of 3.0" w.c. because: $(2 \ 1/2 \ \text{turns}) \ x \ (1.2" \ \text{w.c.}) \ \text{per turn} = 3.0" \ \text{w.c.}$

To adjust the set point on any Cleveland Controls Series AFS Air Switch with Adjustment Range of 0.05 - 2.0" w.c. \pm 0.02" w.c.:

Turn the adjusting screw counter-clockwise until motion has stopped. Next, turn the adjusting screw four complete turns in a clockwise direction to engage the spring. From this point, the **next ten turns** will be used for the actual calibration: **Each full turn represents approximately 0.2" w.c..** *example*:

To set the switch at 0.6" w.c., turn the screw counter-clockwise until travel stops. Then turn four turns in a clockwise direction to engage the spring. A further 2 1/2 turns in a clockwise direction will result in a setting of 0.6" w.c. because: $(2 \ 1/2 \ \text{turns}) \times (0.2" \ \text{w.c.}) = 0.6" \ \text{w.c.}$

To adjust the set point on a Cleveland Controls AFS-460 Manual Reset Air Switch with Adjustment Range of 0.40 - 12.0" w.c. \pm 0.06" w.c.:

Turn the adjusting screw counter-clockwise until motion has stopped. Next, turn the adjusting screw four complete turns in a clockwise direction to engage the spring. From this point, the next ten turns will be used for the actual calibration: **Each full turn represents approximately 1.16" w.c..** *example*:

To set the switch at 2.9" w.c., turn the screw counter-clockwise until travel stops. Then turn four turns in a clockwise direction to engage the spring. A further 2 1/2 turns in a clockwise direction will result in a setting of 3.0" w.c. because: $(2 \ 1/2 \ \text{turns}) \times (1.16" \ \text{w.c.}) = 2.9" \ \text{w.c.}$

Please Note: To properly calibrate a Cleveland Controls Air Switch, a digital manometer or other measuring device should be used to confirm actual set point.