



1936

1996



Continues to Lead



UP TO 98% THERMAL EFFICIENCY

A. O. Smith has delivered innovative hot water solutions for nearly 80 years. As a global leader in water heating, A. O. Smith offers a wide selection of quality residential and commercial water heaters that provide an energyefficient solution.

The Cyclone® family of water heaters is an example of such a solution. Introduced in 1996, the Cyclone is the industry leader when it comes to certified ENERGY STAR ® high efficiency gas water heating. And with the newest member of the Cyclone family; the Cyclone Mxi, innovation continues to lead.





For more information, please visit www.hotwater.com.

FEATURES & BENEFITS OF THE Cyclone MXI



FULLY MODULATING COMBUSTION

- Modulates the firing rate as the demand changes
- Modulating the burner results in higher overall operating efficiencies and longer service life
- Models are available from 120,000 to 499,900 BTU/h

RELIABLE COMPONENTS

- Robust direct spark ignition for years of worryfree operation
- Pre-mix burner system designed for smooth light off and operation

HELICAL COIL HEAT EXCHANGER

- Large surface area for heat transfer maximizes efficiency
- External and internal glassing
- Significantly fewer weld joints result in less opportunity for leaks compared to straight multi-flue designs
- Baffle-free design avoids unwanted restriction and hot spots
- No radiant heat loss at the base results in maintained efficiency over time
- Coil design resists scale build-up
- Coil design results in reduced weight of the water heater

ULTRA HIGH EFFICIENCY

- ENERGY STAR® qualified
- Rated thermal efficiencies of up to 98%

ADVANCED ELECTRONIC CONTROLS

- Easy-to-read diagnostics
- Easily adjustable advanced temperature control
- Optional iCOMM™ remote monitoring

PERMAGLAS® GLASS LINING PROCESS

- Tank is glass coated using an industry exclusive "Ultra Coat™" glassing process
- Coating is applied as a liquid, and the tank is mechanically rotated to ensure all areas are evenly covered to protect against corrosion

EASY INSTALLATION

- Unique design has all components located on top or on the front
- Lightweight design allows for easy maneuverability during installation

POWERED ANODES ON ALL MODELS

- Titanium powered anodes standard on all model sizes
- Powered anodes work in all water conditions, never need replacing and eliminate possibility of strong water odors usually related to conventional anodes

DIRECT VENT LENGTHS

- 120 to 250 models can be direct vented using 3" PVC,
 CPVC or polypropylene pipe up to 50 equivalent feet and 120 feet using 4" pipe
- 300 to 500 models can be vented using 4" pipe up to 70 feet and 6" pipe up to 120 feet

WATER DURABLE

- Approved for operation in a variety of water conditions
- The unique design allows it to maintain efficiency in higher levels of water hardness
- Nearly unaffected by scale build-up due to the burner on top and heat passages well above the bottom of the tank

WATER CONNECTIONS

- 1 ½" top water outlet
- Recirculation loop return connection
- 1 ½" lower front water inlet

FIELD WIRING JUNCTION BOX

- Terminal block for easy 115v wiring connection
- Auxiliary relay
- Built-in surge protection

