Performance Data Sheet

Model: AP510

Use Replacement Cartridge AP517

The concentration of the indicated substances in water entering the system was reduced to a concentration less than or equal to the permissible limit for water leaving the system as specified in NSF/ANSI Standard 42.



System tested and certified by NSF International against NSF/ANSI Standard 42 for the reduction of substances listed below.

Capacity 2000 Gallons (7,571 Liters)

Contaminant Reduction Determined by NSF testing.

Contaminant Reduction	Average Influent	NSF specified Challenge Concentration	Avg % Reduction	Average Product Water Concentration	Max Permissible Product Water Concentration	NSF Reduction Requirements	NSF Test Report
Chlorine Taste and Odor	12.0mg/L	2.0 mg/L ± 10%	75%	0.05 mg/L	N/A	≥ 50%	J-00100863

Application Guidelines/Water Supply Parameters			
Service Flow	1.75 gpm (6.6 lpm)		
Water Supply	Potable Water		
Water Pressure	25 -125 psi (172 – 862 kPa)		
Water Temperature	40° F - 100° F (4.4° C - 38° C)		

It is essential that the manufacturer's recommended installation, maintenance and filter replacement requirements be carried out for the product to perform as advertised. See Installation Manual for Warranty information.

Note: While the testing was performed under standard laboratory conditions, actual performance may vary.

Replacement Cartridge: AP517. For estimated costs of replacement elements please call 1-800-222-7880 or visit our website at www.3Mpurification.com

⚠ WARNING

To reduce the risk associated with ingestion of contaminants:

 Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before and after the system.

CAUTION

To reduce the risk associated with property damage due to water leakage:

- Read and follow Use Instructions before installation and use of this system.
- Installation and use MUST comply with all state and local plumbing codes.
- Do not install if water pressure exceeds 125 psi (862 kPa). If your water pressure exceeds 80 psi, you must install a pressure limiting valve. Contact a plumbing professional if you are uncertain how to check your water pressure.
- Do not install where water hammer conditions may occur. If water hammer conditions exist you
 must install a water hammer arrester. Contact a plumbing professional if you uncertain how to
 check for this condition.
- Do not install on hot water supply lines. The maximum operating water temperature of this filter system is 100° F (38° C).
- Protect filter from freezing. Drain filter when temperatures drop below 40°F (4.4°C).
- The disposable filter cartridge **must** be replaced every **6** months, at the rated capacity or sooner, if a noticeable reduction in flow rate occurs.

Parts and service available from:



3M Purification Inc. 400 Research Parkway Meriden, CT 06450, U.S.A. Tel (800) 222-7880 (203) 237-5541 Fax (203) 238-8701 www.3Mpurification.com

3M is a trademark of 3M Company. © 2011 3M Company. All rights reserved. NSF is a trademark of NSF International INSTR2167 1111