

NEW!

SST Series | SST150, SST250, SST300, SST450 Stainless Steel DHW Indirect Tanks

Models: SST150, SST250, SST300, SST450
Indirect storage tanks with capacities of
40, 65, 80 and 119 gallons



BOSCH
Invented for life



SST, the new stainless steel line of domestic hot water indirect tanks, feature important enhancements such as a welded and passivated stainless steel tank and heat exchanger, and two-inch thick, high-density insulating foam with a tested R value of 13.4. This new series of tanks offer capacities ranging from 40 to 119 gallons to suit all your hot water needs.

Features


- ▶ 316L passivated stainless steel tank interior provides superior durability & longevity, offering resistance to the corrosive tendencies on domestic water
- ▶ 304L high capacity stainless steel coil efficiently transfers high volumes of BTU's from heat source to domestic water stored in the tank, making 1st hour delivery among the industry's best
- ▶ High density CFC/HCFC free polyurethane foam insulation yields the lowest stand-by losses in the industry
- ▶ State-of-the-art six axis programmable robotic welder uses computer guidance to accurately weld all stainless steel fittings and coil to the tank
- ▶ Warranty: limited lifetime tank & parts*

**Copies of original warranties in their entirety are available at
www.bosch-climate.us*

SST

Stainless Steel DHW Indirect Tanks

Technical Specifications	SST150	SST250	SST300	SST450
Part Number	7738001642	7738001643	7738001644	7738001645
Description	Indirect stainless steel DHW tank, 40 gal. (151.4 L)	Indirect stainless steel DHW tank, 67 gal. (253.6 L)	Indirect stainless steel DHW tank, 82 gal. (310.4 L)	Indirect stainless steel DHW tank, 113 gal. (427.75 L)
Design	Vertical	Vertical	Vertical	Vertical
Tank Capacity (L)	40 gals (151.4)	67 gals (253.6)	82 gals (310.4)	113 gals (427.75)
Continuous Rating <i>(at 90°F Rise and 180°F Boiler Temperature)</i>	181 GPH	263 GPH	285 GPH	349 GPH
Continuous Rating BTU/Hr.* <i>(2nd Hr.)</i>	115,000	154,000	171,000	216,000
Continuous Delivery* (GPM)	180 GPH (3.3)	264 GPH (4.4)	288 GPH (4.8)	348 GPH (5.8)
Coil Pressure Drop (Feet of Head)	4.5	5.7	6.1	6.5
Height (A)	56" (1,320.8 mm)	60" (1,524 mm)	70" (1,778 mm)	69" (1,752.6 mm)
Width (B)	20" (508 mm)	24" (609.6 mm)	24" (609.6 mm)	28" (711.2 mm)
Relief Valve: ¾" NPT (C)	48.5" (1,231.9 mm)	52.25" (1,327.15 mm)	61.75" (1,568.45 mm)	60.25" (1,530.35 mm)
Boiler In: 1" NPT (D)	48.5" (1,231.9 mm)	52.25" (1,327.15 mm)	61.75" (1,568.45 mm)	60.25" (1,530.35 mm)
Boiler Out: 1" NPT (E)	25" (635 mm)	28" (711.2 mm)	28" (711.2 mm)	31.75" (106.45 mm)
Cold Water Inlet (F)	8.25" (209.55 mm)	9.25" (234.95 mm)	9.25" (234.95 mm)	9.25" (234.95 mm)
Shipping Weight	105 lbs (47.63 kg)	147 lbs (66.68 kg)	177 lbs (80.28 kg)	213 lbs (96.61 kg)
Weight Full of Water	515 lbs (233.60 kg)	820 lbs (371.95 kg)	921 lbs (417.76 kg)	1,268 lbs (575.15 kg)



*These ratings were obtained with a heat source output as listed in the chart and a Domestic Cold Water Inlet at 58°F. Domestic Temperature Rise at 77°F, a Boiler Temperature Output of 180°F, and a flow rate of 15 gpm. Other results will be obtained under different conditions.

▶ Visit www.Bosch-Climate.us today to learn about everything you need for water heating, geothermal, solar and boiler applications.

▶ Visit www.BoschWayToGrow.com and register for online or on-site product training and get ready to take your business to the next level.

MA. Board Approval #
P1-1010-109



Bosch Thermotechnology Corp.

Londonderry, NH • Ft. Lauderdale, FL • Irvine, CA
General Inquiries: 1-866-330-2725
Technical Support: 1-800-283-3787
www.bosch-climate.us

Copyright© 2012 Bosch Thermotechnology Corp.
All rights reserved.

77799318_05/2012