



WEL-FLO®

Diaphragm Well Tanks: WF Series


125 PSIG Working Pressure

Construction

Shell	Steel
Diaphragm	Butyl
Liner	Polypropylene
System Connection	Malleable Iron
Finish	Light Gray
Air Valve	Projection Welded
Factory Precharge	38 PSIG (2.6 bar)

Application

- Controls pump cycling in residential well water systems.



Performance

Maximum Operating Temperature	200°F (93°C)
Maximum Working Pressure	125 PSIG (8.6 bar)
Maximum Relief Valve Setting	100 PSIG (6.9 bar)
Warranty	5 Year

Stand Models

Model	Tank Volume		Max. Accept. Factor	A Tank Height		B Tank Diameter		C Sys. Conn. Centerline		D Stand Diameter		System Conn. (NPTM)	Shipping Weight	
	Gal	Lit		In	mm	In	mm	In	mm	In	mm		Lbs	Kg
WF-14	14.0	53	0.81	25	635	15	381	1 ¹⁹ / ₃₂	40	12	304	1	25	11
WF-20	20.0	76	0.57	32	813	15	381	1 ¹⁹ / ₃₂	40	12	304	1	33	15
WF-26	26.0	98	0.44	39	991	15	381	1 ¹⁹ / ₃₂	40	12	304	1	36	16
WF-32	32.0	121	0.35	47	1194	15	381	1 ¹⁹ / ₃₂	40	20 ¹ / ₂	521	1	43	20
WF-34	34.0	129	1.00	30	762	22	559	1 ⁵ / ₁₆	49	20 ¹ / ₂	521	1 ¹ / ₄	61	28
WF-44	44.0	167	0.77	36	914	22	559	1 ⁵ / ₁₆	49	20 ¹ / ₂	521	1 ¹ / ₄	69	31
WF-62	62.0	235	0.55	47	1194	22	559	1 ⁵ / ₁₆	49	20 ¹ / ₂	521	1 ¹ / ₄	92	42
WF-81	81.0	301	0.41	57	1448	22	559	1 ⁵ / ₁₆	49	20 ¹ / ₂	521	1 ¹ / ₄	103	15
WF-252	86.0	326	0.39	62	1575	22	559	1 ⁵ / ₁₆	49	20 ¹ / ₂	521	1 ¹ / ₄	114	52
WF-86	86.0	326	0.54	47	1194	26	660	2 ¹ / ₁₆	52	20 ¹ / ₂	521	1 ¹ / ₄	123	56
WF-119	119.0	450	0.39	62	1575	26	660	2 ¹ / ₁₆	52	20 ¹ / ₂	521	1 ¹ / ₄	166	75

All dimensions and weights are approximate.

Job Name _____	Notes _____
Engineer _____	_____
Contractor _____	_____
P.O. No. _____	_____
Sales Rep. _____	_____
Model No. _____	_____

