


Multi/Split System Submittal Data

Wall Mounted Indoor Unit - Multi Air Conditioner

CS-MKS7NKH

Job Name: _____
 Location: _____
 Engineer: _____
 Submitted to: _____
 Submitted by: _____
 Reference: _____

Approval: _____
 Date: _____
 Construction: _____
 Unit #: _____
 Drawing #: _____



General Data (at 230V)

Power	V/P/Hz	230/1/60
Circuit Ampacity	(A)	15
Fuse Size, Max.	(A)	20
Running Amps	(A)	.15
Power Input	(W)	35

Indoor Unit

Fan type	Cross Flow
Dia. & Length (in.) - No. Speeds	D3-11/16 L24-31/32 - 1
No. Speeds	3 & Auto
No. Poles	(RPM, High) 8 - 1100
No. Motors	(W) 47 - 1
CFM	(HI) 259
Operation Sound	(HI/Med/Lo/QT* dB-A) 34/31/28/23

Coil Type	Aluminum Plate Fin & Copper Tube
Fin Type - Pipe Type	Slit Plate - Inner Riffled
Rows - F.P.I.	2 - 19.5
Face Area	(sq.ft.) 2.02
Tube Size	(in.) 9/32"
Drain Connection Size	(in.) 23/32"

Refrigerant	R410A
Line Size	(in. O.D. Discharge) 1/4"(Flare)
Line Size	(in. O.D. Discharge) 3/8"(Flare)

Dimensions	(in.) H x W x D
Indoor Unit	(Uncrated) 11-7/32 x 32-15/32 x 7-7/16
	(Crated) 13-25/32 x 35-7/16 x 10-1/32

Weight	Indoor
Net Shipping	(lbs.) 19.8
	(lbs.) 24.3

Shipping Volume	(cu.ft.) Indoor 2.82
-----------------	----------------------

Performance Data @ ARI Standard Conditions (230V)

Cooling		
Total Capacity	(BTU/H)	9,000
Moisture Removal (HI)	(Pint/H)	3.4

Feature

Controls	Microprocessor
Remote Controller	LCD Wireless Type, Temp. Sensor Built In
Temperature Control	IC Thermostat
Timer	24 Hr. Program, 1 Hr. Off
Night Setback	Built-In
Air Louver	(Horizontal) Manual
	(Vertical) Automatic
Power Failure Automatic Restart	Built-In
Heating/Cooling Automatic Changeover	-
Self-Diagnosis	Built-In
Quiet Operation	Built-In
Air Filter	Washable, Anti-Mold
Ion Generator	Equipped
Air Clean Apatite Filer	Standard

Option

Refrigerant Line Set	Available
Fresh Air Intake	N/A
Air duct Extension	N/A
Indoor Frame Extension	N/A
Condensate Drain Pump	Available
Non-Removeable Remo-con Bracket	Available

Dimensions


Operating Range

		IndoorAirIntakeTemp.	OutdoorAirIntakeTemp.
Cooling (CM Model)	Maximum	95F DB/71F WB	115F DB
	Minimum	67F DB/57F WB	67F DB

Note (CLM Model):

1 32F DB: When combined with KMS1872 or KMS2472

23F DB: When combined with KMS0772, KMS0972, or KMS1272



1 unit = 2000/1000000