



Lochinvar®
High Efficiency Water Heaters, Boilers and Pool Heaters

**COPPER-FIN®
BOILER
Submittal Sheet
CBA-Sub-06**

COPPER-FIN GAS BOILERS (MODELS CB 315 - 500)

JOB NAME _____
LOCATION _____
ARCH./ENGR. _____
MECH. CONTRACTOR _____
MODEL NO. _____
TYPE GAS _____
Btu/hr INPUT _____ **Btu/hr OUTPUT** _____
NOTES

Standard Features

- 84% A.F.U.E.
- ASME Copper Finned Tube Heat Exchanger
- Gasketless Heat Exchanger Design
- 82% Thermal Efficiency
- ASME Copper Finned Tube Heat Exchanger
- Gasketless Heat Exchanger Design
- Two Stage Intermittent Electronic Ignition
- 160 PSI Working Pressure
- Pump Relay
- Diagnostic Flash Codes
- Two Stage Solid State Temperature Control
- Two Stage Gas Valve with Built-In Manual Shut-Off
- Automatic Reset High Limit
- ASME Pressure Relief Valve
- Temperature & Pressure Gauge
- Built-In Draft Diverter
- CSA Design Certified for Alcove Installation
- CSA Design Certified for Installation on Combustible Floor
- Stainless Steel Burners
- Loch-Heat Ceramic Tile Combustion Chamber
- 24 Volt Control System
- 10 Year Limited Warranty on Heat Exchanger
(See warranty for details)

Optional Equipment


Place an X in the box by all options that apply

- Adjustable High Limit w/ Manual Reset
- Contacts on any Failure
- Contacts for Air Louvers
- Flow Switch
- Outdoor Air Reset Control
- Low Water Cut-Off
- Multi-Stack Frame
- Pump Delay/Freeze Protection
- MP² Sequencer
- Low Temperature Valve

Firing Controls

- M9 - Two-Stage Intermittent Spark Ignition (Standard)
- M13 - GE GAP/FM/IRI
- M7 - California Code

Copper-Fin Gas Boiler Dimensions & Specifications



Copper-Fin Boiler					Dimensions & Specifications						
Model Number	Input MBH	Thermal Efficiency %	Output MBH	Net I=B=R MBH	A	B	C	D	Gas Conn.	Vent Size	Ship. Weight
CBN315	315	82.0	258	224	29-1/2"	32-1/4"	21-1/2"	16-1/4"	3/4"	8"	245
CBN360	360	82.0	295	257	29-1/2"	35-1/4"	21-1/2"	17-3/4"	1"	9"	255
CBN399	399	82.0	328	285	29-1/2"	44-1/2"	22"	22-1/4"	1"	10"	320
CBN500	500	82.0	410	357	34-1/2"	52-1/2"	22"	26-1/4"	1"	10"	345

Notes: Change 'N' to 'L' to denote L.P. gas models
 No deration for L.P. models.
 Water Connections are 2" NPT on 6-1/4" centers.
 Performance data is based on manufacturer test results.



Lochinvar®
 High Efficiency Water Heaters, Boilers and Pool Heaters



Lochinvar Corporation • 300 Maddox Simpson Pkwy • Lebanon, TN 37090 • 615-889-8900 / Fax: 615-547-1000

www.Lochinvar.com