

# SharkBite® Water Hammer Arrestor

## DESCRIPTION

The SharkBite® Water Hammer Arrestors are engineered devices that provide a maintenance free continuous protection system against detrimental destructive forces generated by the immediate cessation of water flowing in the water distribution system. The SharkBite® Water Hammer Arrestor is engineered to expressly be used with SharkBite®. The SharkBite® Water Hammer Arrestor can be installed horizontally and vertical and can be connected in seconds to copper tubing, and CTS CPVC and PEX.

## FEATURES AND BENEFITS

Instant push-fit connections for increased ease-of-use:

*No soldering, clamps, unions, or glue required.*

Designed for vertical and horizontal installation:

*Flexible installation options in new or existing plumbing systems.*

Listed by ASSE:

*Inspector friendly, peace of mind.*

Water tight Joint:

*Seal that is permanently water tight.*

## SPECIFICATION DATA

### Performance:

Maximum pressure . . . . . 200 psi

Maximum temperature . . . . . 200°F (93°C) (water)

Service . . . . . Water

### Hammer Arrestor Materials:

Barrel . . . . . Type "K" hard drawn copper

Piston . . . . . Brass

Cap . . . . . Brass

O-rings . . . . . EPDM

### SharkBite® Materials:

Body . . . . . DZR brass

O-ring . . . . . EPDM



Grab ring . . . . . Stainless steel

Tube support liner . . . . . Polysulfone

## CONNECTIONS

SharkBite® . . . . . 1/2", 3/4" & 1"

Cash Acme Size	Fixture Units
1/2"	1-11
3/4"	12-32
1"	33-60



Product Number	A	B	C
22630	1/2"	2.72"	6.37"
22631	1/2"	2.72"	7.37"
22632	3/4"	3.24"	9.71"
22633	1"	3.84"	9.60"