



T and TV Expansion Tanks

Cash Acme's T Series Expansion Tanks are designed for heating systems applications.

Cash Acme's TV Series Floor Standing Expansion Tanks are designed for heating systems applications.

- Welded Construction: *Ensures long and reliable service.*
- Heavy duty Butyl diaphragm and epoxy paint finish: *Long lasting and resistant to external elements.*
- Provides place for expanding water: *Eliminates damage to the boiler and piping.*
- The tank connection has a plastic sleeve: *Protects against corrosion.*
- All models are factory precharged to 12 psi: *Efficient and economical.*
- Gives water a place to flow when thermal expansion occurs: *Eliminates costly and serious effects such as noisy water hammering pipes and damaged connections.*
- Corrosion resistant base.




T Expansion Tank




TV Expansion Tank

TYPICAL INSTALLATION



T Expansion Tank




TV Expansion Tank




T and TV Expansion Tanks


T Expansion Tank



TV Expansion Tank



MODELS/SIZES



T Expansion Tank

TV Expansion Tank

In-Line Models	Capacity (gal)	Acceptance Volume (gal)	Conn. NPTM	Max. Work. Pressure (psig)	Factory Precharge	Diameter	Height	Weight
T-15	2.0	1.50	1/2"	100	12	8.38"	12.50"	5.0
T-30	5.0	3.75	1/2"	100	12	11.38"	14.75"	8.0
T-60	7.0	4.60	1/2"	100	12	11.38"	21.13"	11.0
T-90	15.0	10.50	1/2"	100	12	15.38"	15.75"	22.0
Stand Models								
TV-30	15.0	10.5	1/2"	100	12	15.38"	24.75"	25.0
TV-40	20.0	13.5	1/2"	100	12	15.38"	32.75"	32.0
TV-60	36.0	21.0	1/2"	100	12	20.0"	32.63"	45.0
TV-90	52.0	34.0	1/2"	100	12	23.38"	38.63"	80.0
TV-110	86.0	61.0	1/2"	100	12	23.38"	32.63"	99.0
TV-160	96.0	64.0	1/2"	100	12	23.38"	59.00"	99.0