

March 2015 http://media.diversitech.com/doc/DOC04039.pdf

Page 1 of 2

Condensate Pumps

CP-22 Pumps

Suitable for use with condensate from high efficiency condensing furnaces and boilers which produce acidic condensate. 22ft of lift compared to the typical 20ft. Features include vibration dampening feet and motor mounts, metal hang tabs, four inlet holes, a clear indicator display, a float switch and check valve, and pan pill dispenser. Integrating the CP-22 into your system is easy. 1/4in. quick connect terminals provide easy connection to the built in overflow switch. 3 terminals are provided allowing flexibility to connect air-handler shut-down and optional alarm as needed. The new CP-22LP comes packed with all the same great features found in the CP-22, but now in a low profile package. This pump is only 4 3/8in. tall so it's a good fit for those instances where space is at a premium. The shorter reservoir holds 1/3 gallon. Suitable for use with condensate up to 160 degree F. UL Listed File Numbers E253155 and E258186.



| Catalog No. | Description | UOM | Order Multiple | List Price |
|-------------|---|-----|-------------------|------------|
| CP-22 | CP-22 Condensate Pump, 22ft. lift, 120V | EA | 6 | \$115.56 |
| CP-22-230 | CP-22 Condensate Pump, 22ft. lift, 230V | EA | 6 | \$140.12 |
| CP-22-230T | CP-22 Condensate Pump, 22ft. lift, w/ 20ft. of 3/8in. CVT, 230V | EA | 6 | \$145.04 |
| CP-22T | CP-22 Condensate Pump, 22ft. lift, w/ 20ft. of 3/8in. CVT, 120V | EA | 6 | \$121.76 |

CP-22 Low Profile Pumps

The new CP-22LP comes packed with all the same great features found in the CP-22, but now in a low profile package. This pump is only 4 3/8in. tall so it's a good fit for those instances where space is at a premium. The shorter reservoir holds 1/3 gallon. Suitable for use with condensate up to 160 degree F. UL Listed File Numbers E253155 and E258186.

| up to 100 degree 1. Of Listed File Numbers £255155 and £256166. | | | | |
|---|--|-----|-------------------|------------|
| Catalog No. | Description | UOM | Order Multiple | List Price |
| CP-22LP | CP-22 Condensate Pump, 22ft. lift, low profile, 120V | EA | 6 | \$132.76 |
| CP-22LP-230 | Condensate Pump, low profile, 22ft. lift, 230V | EA | 6 | \$144.88 |

General Purpose Pumps

The DiversiTech CP-16 condensate pump is an economical alternative that's based off of the proven CP-22 design. More compact than the CP-22, it's designed to lift to a maximum of 16 feet. The CP-16 shares many of the great features of the CP-22, including hang tabs, four inlet holes, float switch, overflow switch, and a check valve. UL Listed File Numbers E253155 and E258186.



| Catalan Na | Description | 110 |
|-------------|---|-----|
| Catalog No. | Description | UC |
| CP-16 | CP-16 Condensate Pump, 16ft. lift, 120V | E |
| CP-16-230 | Condensate Pump, 16ft. lift, 230V | E |

| UOM | Order Multiple | List Price |
|-----|-------------------|------------|
| EA | 6 | \$103.80 |
| EA | 6 | \$115.76 |

Condensate Pumps

Pump Parts & Accessories

Check valve installs easily and prevents water from travelling backwards into the pump and overflowing.



| Catalog No. | Description | UOM | Order Multiple | List Price |
|-------------|--|-----|-------------------|------------|
| CP-CV | Replacement Check Valve for CP-22 | EA | 1 | \$7.40 |
| CP-CV14 | Replacement Check Valve - 1/4in. | EA | 1 | \$11.36 |
| CP-CVCF | Replacement Check Valve - 3/8in. Compression fitting | EA | 1 | \$21.20 |

Merchandising

Counter Mats

Each counter mat has a specific product focus. The mats are encapsulated with a tough wearing clear plastic cover, and a non-skid rubber back. Most mats are 20in. by 16in.



| Catalog No. | Description | UOM | Order Multiple | List Price |
|--------------|-----------------------------|-----|-------------------|------------|
| MKT-MAT-PUMP | Condensate Pump Counter Mat | EA | 1 | \$0.00 |