


Dimensional Data (inches and [ mm ]) are Subject to Manufacturing Tolerances and Change Without Notice



Product	'A' Connections	'E' Body Height	Great Open Area Sq. In [cm <sup>2</sup> ]
___ FD2290-NH2	2 [51] No-Hub	3-1/8 [79]	7 [45]
___ FD2290-NH3	3 [76] No-Hub	3-1/8 [79]	
___ FD2290-NH4	4 [102] No-Hub	3-1/8 [79]	
___ FD2290-PO2	2 [51] Push-On	3-5/8 [92]	
___ FD2290-PO3	3 [76] Push-On	3-5/8 [92]	
___ FD2290-PO4	4 [102] Push-On	3-5/8 [92]	

**FD2290 Adjustable Finished Area Floor Drain**  
Recommended for finished floor areas where a membrane is generally used. This drain is designed for foot traffic and light cart applications. Complete with cast iron body, clamp collar and adjustable nickel bronze strainer assembly.

**OPTIONS:**

- \_\_\_ -CP Chrome Plated Strainer
- \_\_\_ -P 1/2 [13] Trap Primer Connection
- \_\_\_ -PB Polished Brass Strainer
- \_\_\_ -R6 6 [152] Diameter Nickel Head Assembly
- \_\_\_ -R7 7 [178] Diameter Nickel Head Assembly
- \_\_\_ -R8 8 [203] Diameter Nickel Head Assembly
- \_\_\_ -VP Vandal Proof

**Typical Installation**

