



Multi Zone Submittal Data

Indoor: CS-S9NKUW-1
Wall Mounted Air Conditioner's

Job Name: _____
Location: _____
Engineer: _____
Submitted to: _____
Submitted by: _____
Reference: _____

Approval: _____
Date: _____
Construction: _____
Unit #: _____
Drawing #: _____

Power	V/PH/Hz	230/208/1/60
Circuit Ampacity	(A)	15
Fuse Size, Max.	(A)	15
Indoor Unit		
Fan type		Cross Flow
No. Speeds		5
RPM	(High)	
Motor Output	(W)	40
CFM	(QLo/Lo/Me/Hi/SHi)	199/239/321/400/442
Indoor Sound Rating	(Hi) (dB-A)	40
Coil Type		Aluminum Fin & Copper Tube
Fin Type - Pipe Type		Slit Plate - Inner Rifled
Rows - F.P.I		2-19
Face Area	(sq.ft)	
Drain Connection Size	(in.)	5/8"
Features		
Wireless Remote Controller Standard		
Wired Remote Controller (CZ-RD516C) Optional		
Controls		Microprocessor
Remote Controller	LCD Wireless Type, Temp, Sensor Built In	
Temperature Control		IC Thermostat
Air Louver	(Horizontal)	Manual
	(Vertical)	Automatic
Power Failure Automatic Restart		Built-In
Self-Diagnosis		Built-In
Air Filter		Washable, Anti-Mold

Refrigerant				R410A
Control			Electric Expansion Valve	
Connection				Flare
Line Size	(in. O.D. Discharge)			1/4"
Line Size	(in. O.D. Suction)			3/8"
Dimensions	(in.)	Height	Width	Depth
Indoor Unit	(Uncrated)	11-7/16"	34-9/32"	8-1/16"
Weight				Indoor
Net	(lbs.)		20	
Shipping	(lbs.)			
Performance Data @ ARI Standard Conditions (230/208V)				
Cooling				
Total Capacity	(BTU/H)			10200
SEER				17.5
Dehumidification	(Pints/H)			1.3
Operating Range				
Cooling	Maximum		Indoor Air Intake Temp.	
	Minimum		90F DB/74F WB	
			60F DB/52F WB	

Indoor Dimensions

