

SharkBite® Ball Valve

DESCRIPTION

The Cash Acme SharkBite® Ball Valves are high quality forged brass ball valves with SharkBite® connections. The SharkBite® connections allows the user to connect the ball valves to copper tubing, CPVC and Pex in seconds with relative ease.

FEATURES AND BENEFITS

Convenient single lever control:

Makes them easy to use and encourages shut-off of water supply.

Full Port Ball Valve:


Allows water to flow freely through valve.

Instant push-fit connections for increased ease of use:

No soldering, clamps, unions, or glue required.

Valve assembled to strict quality standards:

Measured thread engagement, measured torque.



Α

3.06"

3.62"

4.40"

В

3.70"

3.70"

4.66"

SPECIFICATION DATA

Performance:

Maximum pressure 200 psi Maximum temperature 200°F (water)

Service Water

Ball Valve Materials:

Body.....Brass Seat Ring PTFE

Ball Brass, chrome plated

Body End Retainer Brass Stem.....Brass O-ring.....NBR PackingPTFE Packing Nut.....Brass

HandleZinc plated steel Handle Nut.....Zinc plated steel

SharkBite® Materials:

Body......DZR brass O-ring.....EPDM Grab Ring.....Stainless steel


Tube support liner Polysulfone

Dimensions

1/2" (22222-0000)

3/4" (22185-0000)

1" (22223-0000)



Α	В
3.75"	4.5"

CONNECTIONS

CERTIFICATIONS

The SharkBite® Ball Valve 1/2", 3/4" and 1" are certified to IGC-157/NSF-61, and listed by IAPMO.

