

UP TO **92.1% AFUE PERFORMANCE**



Air Conditioning & Heating

GKS9 HIGH-EFFICIENCY, MULTI-SPEED GAS FURNACE



Thank goodness for Goodman.®



Air Conditioning & Heating

FOR RELIABLE WARMTH AND MONEY-SAVING ENERGY EFFICIENCY.

As a homeowner, you try to find a balance between your family's comfort and your monthly energy costs. To meet those needs, we've developed the Goodman® brand GKS9 Energy-Efficient Multi-Speed Gas Furnace. What should you expect from your Goodman brand GKS9 Energy-Efficient Multi-Speed Gas Furnace? How about a superior combination of performance, efficiency and affordability? That's just what you'll get with Goodman. Whether it's the coldest day of the year or any day of the year, with the Goodman brand GKS9 Gas Furnace you'll be saying, **"Thank goodness for Goodman!"**



ENJOY THE COMFORT AND EFFICIENCY

Energy efficiency is key to controlling the cost of heating your home. This furnace's 92.1% AFUE rating means 92.1 cents of every \$1.00 of heating energy expense warms your home. Some older central heating systems rate at 60% AFUE, meaning only 60 cents of every \$1.00 of heating energy expense warms your home. The remaining 40 cents is lost energy – wasteful and expensive.

RELIABILITY AND LONG LIFE

The heart of any furnace is the heat exchanger. Our aluminized-steel tubular heat exchanger and stainless-steel recuperative coil have been tested to industry standards.

For further safety and reliability, we also include a quiet, efficient Hot Surface Igniter that helps ensure safe start-ups and maximum igniter life.

QUIET YOU CAN COUNT ON

Your Goodman brand GKS9 Furnace uses a multi-speed blower motor and sound-isolated blower assembly to reduce the noise levels common in other furnaces without these features. Add an insulated, heavy-gauge steel cabinet, and the result is... quiet comfort.

Unmatched combination of performance, efficiency and affordability. That's just what you'll get with Goodman.

THE HEART OF COMFORT



The award-winning design of the primary heat exchanger in the Goodman brand GKS9 Gas Furnace is unique. It's constructed from tubular aluminized-steel and formed into a dual-diameter configuration. Furthermore, the use of wrinkle-bend technology results in an extremely durable heat exchanger. A heat exchanger often is considered the essential component of any gas furnace. Additionally, this gas furnace has a stainless-steel secondary heat exchanger. This combination offers one of the best levels of reliability, durability, and efficiency you'll find within the Goodman brand.



IMPRESSIVE FEATURES AND BENEFITS:

GOODMAN® BRAND GKS9

MULTI-SPEED HIGH-EFFICIENCY GAS FURNACE

- Aluminized-Steel Tubular Primary Heat Exchanger; Stainless-Steel Secondary Heat Exchanger
- Quiet, Efficient Hot Surface Igniter
- Powder-Paint Finish
- Corrosion-Resistant Vent Blower
- Electronic Ignition Control
- Multi-Speed Blower
- Insulated Cabinet



Talk to your Goodman brand dealer about opportunities to optimize the efficiency of your new unit.

OUTSTANDING WARRANTY* PROTECTION



* Complete warranty details available from your local dealer or at www.goodmanmfg.com. To receive the Lifetime Heat Exchanger Limited Warranty (good for as long as you own your home) and 10-Year Parts Limited Warranty, online registration must be completed within 60 days of installation. Online registration is not required in California or Quebec.

ADDITIONAL INFORMATION

Before purchasing this appliance, read important information about its estimated annual energy consumption, yearly operating cost, or energy efficiency rating that is available from your retailer.



Thank goodness for Goodman®

MODEL	HEATING EFFICIENCY AFUE	LIMITED PARTS WARRANTY* COVERAGE			COMFORTNET [®] CONTROL SYSTEM COMPATIBLE	BLOWER MOTOR	GAS VALVE	TYPE OF IGNITER	TUBULAR HEAT EXCHANGER
		10 YEAR UNIT REPLACEMENT HEAT EXCHANGER LIMITED WARRANTY	10 YEAR PARTS LIMITED WARRANTY	LIFETIME HEAT EXCHANGER LIMITED WARRANTY					
GKS9	Up to 92.1%		•	•		Multi-Speed	Single-Stage	Hot Surface	•
GMVM96	Up to 96%	•	•	•		Variable-Speed	Modulating	Silicone Nitride	•
GCV96	Up to 96%	•	•	•	•	Variable-Speed	Modulating	Silicone Nitride	•
GMVC95	Up to 95%	•	•	•	•	Variable-Speed	Two-Stage	Silicone Nitride	•
GCVC9/95 Downflow	Up to 95%	•	•	•	•	Variable-Speed	Two-Stage	Silicone Nitride	•
GMH95	Up to 95%	•	•	•		Multi-Speed	Single-Stage	Silicone Nitride	•
GCH9/95 Downflow	Up to 95%	•	•	•		Multi-Speed	Single-Stage	Silicone Nitride	•

*Complete warranty details available from your local dealer or at www.goodmanmfg.com. To receive the 10-Year Unit Replacement Heat Exchanger Limited Warranty, Lifetime Heat Exchanger Limited Warranty (good for as long as you own your home) and 10-Year Parts Limited Warranty, online registration must be completed within 60 days of installation. Online registration is not required in California or Quebec.

GOODMAN: THE RECOGNIZED INDUSTRY LEADER

Every Goodman® brand heating and air conditioning system is designed, engineered, and manufactured with pride. All employees follow strict, quality-driven processes to ensure that all Goodman products offer the legendary performance that has made the brand a recognized leader in the industry. This attention to quality has resulted in the Goodman family of companies becoming the second largest unit manufacturer of residential air conditioning and heating systems in North America.

THE GOODCARE® EXTENDED SERVICE PLAN

For even greater peace of mind, ask your dealer or visit our web site at www.goodmanmfg.com for more details about **GoodCare**, an affordable Parts and Labor Extended Service Plan for your entire Goodman brand HVAC system.†

† Extended Service Plans not available in all states. Ask your dealer for full details.

GoodCare†
EXTENDED SERVICE PLAN
Provides Years of Worry-Free Coverage



Goodman®

Air Conditioning & Heating



Our continuing commitment to quality products may mean a change in specifications without notice.
© 2012 Goodman Manufacturing Company, L.P. • Houston, Texas

www.goodmanmfg.com



CB-GKS9 02-12