or Residential and Commercial Applications			
Job Name	Engineer / Architect		
Job Location	Wholesaler		
Submittal Date	Contractor		

DRS83 Integral Shut-Off Straight Stop w/ Screwdriver Slot – Female Iron Pipe x Male Iron Pipe

Use: For use in potable water distribution systems. Not intended for recirculating water systems that produce continuous use temperatures above 115° F. For those applications, use BrassCraft KT series ball stops

Design Features:

- Machined one-piece brass body provides strength, durability and long-lasting performance
- **Screwdriver slot handle** helps protect against accidental stop operation during rough-ins and in general use


Operating Specifications:

Temperature: 40°- 140° F

Pressure: 125 psi maximum

MATERIAL SPECIFICATIONS		
Valve Body	C36000 brass	
Screwdriver Slot Stem	C36000 brass	
Bib & Packing Washers	Nitrile or EPDM rubber	
Packing Nut	C36000 brass	

PART DIMENSIONS (Inches)				
Model	DIM. A	DIM. B		
DRS83	1.33	2.10		



Part Listing:

Ш	DRS83 C	1/2" F.I.P. x 1/2" M.I.P. with screwdriver slot, chrome plated
	DRS83 R	1/2" F.I.P. x 1/2" M.I.P. with screwdriver slot, rough brass
	DRS83 RBT	1/2" F.I.P. x 1/2" M.I.P. with screwdriver slot, rough brass, bulk, plain tray
	DRS83 R1	1/2" F.I.P. x 1/2" M.I.P. with screwdriver slot, rough brass, window tray

Listings & Certifications:

- IAPMO listed to ASME A112.18.1-05 /CSA B125.1-05 (File # 0645)
- CSA listed to ASME A112.18.1-05 / CSA B125.1-05 (File # 204593)





