


Dimensional Data (inches and [ mm ]) are Subject to Manufacturing Tolerances and Change Without Notice



Model Number	Approx Wt. Lbs. [kg]	Dimension in Inches	
		R	U
____ JP2700-4-6-EXT	11 [5]	13 1/4 [337]	9 5/8 [244]
____ JP2700-7-6-EXT	13 [6]	14 5/8 [371]	11 5/8 [295]
____ JP2700-10-6-EXT	15 [7]	16 5/8 [422]	13 3/4 [349]
____ JP2700-15-6-EXT	17 [8]	18 5/8 [473]	16 1/2 [419]
____ JP2700-20-6-EXT	19 [9]	21 1/2 [546]	17 [432]
____ JP2700-25-6-EXT	21 [10]	23 1/2 [597]	19 5/8 [498]
____ JP2700-35-6-EXT	23 [10]	25 3/8 [645]	22 1/4 [565]
____ JP2700-50-6-EXT	25 [11]	27 1/4 [692]	24 1/4 [616]
____ JP2700-75-6-EXT	27 [12]	33 3/8 [848]	28 3/8 [721]
____ JP2700-100-6-EXT	30 [14]	40 1/8 [1019]	33 3/8 [848]

**JP2700-xx-6-EXT Grease Trap Extension**  
Corrosion-resistant coated fabricated steel.

- \* Standard 6 [152] Increments
- \* Ability to use more than one (Stackable)