



FAN BLADE ACCESSORIES

HEX HUB FEATURES

- Sizes to fit most applications
- Simple screw design
- Zinc plated steel
- Pre-tapped holes with mounting and set screws started



INTERCHANGEABLE HEX HUBS		
PART NO.	BORE	NO. SET SCREWS
H5	5/16	1
H6	3/8	1
H8	1/2	2
H10	5/8	2

Packaged 12 per carton.

BUSHING FEATURES

- Two bolt design
- Two 1/4-20 x 3/4" cap screws provided
- Malleable iron construction
- For 1/2"-13/8" bore ranges



SPLIT TAPERED BUSHINGS "H" SERIES	
PART NO.	BORE
STB1	1/2
STB2	5/8
STB3	3/4
STB4	7/8
STB5	1
STB6	1 1/8
STB7	1 3/16
STB8	1 3/8

Packaged one per kit.

FAS MOUNT BRACKET KITS

FM50

Motor diameter 5.0"
Bolt circle 9" and 10.18"



FM55

Motor diameter 5.5"
Bolt circle 9" and 10.18"

These kits are designed for direct drive blower motors using the flexible bracket mounting arrangement.
Grommets and eyelets are included.

BAND MOUNTING KITS

LUG KITS

PART NO.	MOTOR DIA.	LUG SIZE	BOLT CIRCLE RANGE
N055L	5.5"	Large	8 1/8 - 12 1/8
N055S	5.5"	Small	6 7/8 - 8 1/8
KIT34	3.3"	Large	4 11/16 - 9 7/8
KIT50	5.0"	Large	6 7/16 - 11 11/16
KIT49	3 small lugs for Kit 55S		
KIT150	4 grommets to fit lugs on Kits 34, 49, 50, 55L, 55S		
N050L	4.4" & 5.0"	Large	6 1/2 - 11 8/16
N033L	3.3"	Large	4 1/2 - 10
KIT315	5.0"	Large	10 9/50
KIT317	5.6"	Large	10 9/50



N055L, N055S,
KIT34, KIT50



KIT150




KIT49



N050L, N033L




KIT315, KIT317



FM55 replaces this type bracket

NOTE: Thermally protected • UL recognized • CSA or ULc certified
Rotation is determined by looking at shaft end. Shaft length is measured from motor face.



CONDUIT BOXES

KIT142

Black box for 3.3" diameter motors.

Packaged one per kit.



KIT144

Gray, tie-rod mountable box for 4.4", 5.0" and 5.6" diameter motors.

Packaged one per kit.



CONDUIT KITS

KIT100

For 5/16" and 3/8" Greenfield (flexible conduit).

Packaged two per kit.



KIT102


3/8" Conduit Connector Allen Stevens type, complete with mounting screws.

Packed three per kit.



BLOWER ACCESSORIES

INLET SCREENS



4004

A = 3.125

B = 4.50

C = 4.188

4000

A = 4.72

B = 6.125

C = 5.75

INLET 4004

For Air Rotors of less than 3 7/8" diameter, Inlet 4004 can be used on the following blowers:

50746-D500, 50747-D230, 50747-D401, 50747-D500, 50747-D600, 50748-D500, 50748-D700, 50752-D230, 50752-D500, A069, A071, A073, A075, A081, A083, B23617 or B23618

Packaged one per kit.

INLET 4000

For Air Rotors of less than 4" to 5 1/2" diameter, Inlet 4000 can be used on the following blowers:

50755-D230, 50755-D500, 50756-D230, 50756-D500, 50757-D500, A159 or A161

Packaged one per kit.

FLANGES

Any flange below may be used on blower models 50747-D600, 50748-D700, B23617, B23618, A073 or A081.

KIT280

Meeting hole diameter .281"

Packaged one per kit.



KIT282

Meeting hole diameter .136"

Packaged one per kit.

KIT284

Packaged one per kit.





RESILIENT MOUNTING BASE INDEX

FASCO MODEL NO.	RECOMM. BASE	FASCO MODEL NO.	RECOMM. BASE	FASCO MODEL NO.	RECOMM. BASE	FASCO MODEL NO.	RECOMM. BASE	FASCO MODEL NO.	RECOMM. BASE	FASCO MODEL NO.	RECOMM. BASE
D112	517*	D264	408*	D491	558	D783	461	D920	595	D1246	435
D117	386	D277	479	D492	558	D784	558	D923	492	D1709	595*
D148	354	D290	435*	D493	558	D785	542	D927	435	D1710	705*
D150	492*	D312	492	D494	492	D786	595	D928	435	D1745	558
D151	492*	D314	517*	D495	492	D787	492	D929	558*	D1748	461
D152	492*	D316	461*	D497	542	D788	558	D930	558*	D1749	461
D154	558	D329	435	D635	435	D789	592	D935	558	D1853	492
D156	479*	D333	386*	D655	435	D807	435	D937	461	D1910	595
D158	479	D335	408	D656	479	D812	492	D939	461	D1911	558
D160	479	D336	435	D658	479	D814	435	D940	595*	D2700	595
D164	479*	D337	435	D701	595	D816	461	D951	595*	D2701	558
D166	479*	D338	492	D703	558	D818	705*	D966	517*	D2702	595*
D174	417	D339	492	D711	595	D821	542	D967	558	D2703	595*
D176	354*	D347	386	D721	461	D823	595	D968	595	D2704	595*
D178	417	D354	479	D723	517	D825	705	D970	595	D2705	705
D221	417	D356	417	D725	461	D831	705*	D971	542	D2814	595*
D224	435	D382	386	D726	558*	D838	595	D972	492	D2816	NONE
D236	435	D389	408	D727	479	D860	595	D973	461	D2817	595*
D245	558	D435	517*	D728	595	D870	542	D974	595	D2818	NONE
D247	479	D474	542	D729	595	D879	461	D975	461	D2832	595*
D249	354	D480	542	D730	595	D896	435	D1015	435	D2833	595
D250	435	D481	542	D733	492	D897	435	D1016	479	D7745	517
D252	354	D482	492	D735	595	D902	595	D1025	492	D7748	492
D253	354	D483	492	D737	517	D910	595	D1033	479	D7749	435
D254	417	D484	492	D739	492	D911	558	D1042	492	S2846	705
D255	417	D485	492	D745	517	D912	479	D1046	386	S2848	NONE
D256	479*	D486	517*	D746	517	D913	479	D1051	408	S156	435
D257	417	D487	517*	D747	542	D914	595	D1061	492		
D258	435	D488	517	D748	492	D915	595	D1065	408*		
D260	479	D489	542	D780	517	D916	595	D1086	435		
D261	461	D490	558	D782	492	D918	479	D1089	435		

*May need to reverse one or more mounting rings.

CRADLE BASE "B" DIMENSION	3 1/2" BASE NO.	3" BASE NO.
3.54	35-354	30-354
3.86	35-386	30-386
4.08	35-408	30-408
4.17	35-417	-
4.35	35-435	30-435
4.61	35-461	30-461
4.79	35-479	30-479
4.92	35-492	30-492
5.17	35-517	30-517
5.42	35-542	30-542
5.58	35-558	30-558
5.95	35-595	30-595
7.05	35-705	30-705


NOTE: The current base numbering system uses the first two numbers to indicate shaft height (30 is 3.0" and 35 is 3.5") and the last three numbers represent distance between cradle arms (386 is 3.86" etc.). Example: 35-417 has a 3.5" shaft height and 4.17" cradle base. To achieve the shaft height listed, the 2 1/2" diameter rings must be used.

For motors not listed : Add .8 to "A" dimension of 4 7/16" diameter motors for base "B" dimension.
Add .9 to "A" dimension of 5" diameter motors for base "B" dimension.
Add .5 to "A" dimension of 5 5/8" diameter motors for base "B" dimension.



CLAMP6004

Extra base clamps. Two base clamps ship with each base.



-specify shaft height 3.00" or 3.50" and motor model.

Thermally protected • UL recognized • CSA or ULc certified
NOTE: Rotation is determined by looking at shaft end. Shaft length is measured from motor face.



FOR 3.3" DIAMETER MOTORS

KIT216

Special end plate for 3.3" diameter motors for base mounting.
Use with Kit 180 mounting rings.
Packaged one per kit.



KIT225

Triangular bracket with grommets for 3.3" diameter motors.
Packaged one per kit.



MOUNTING CUP

KIT265

Used to mount 3.3" motors to some blower housings.
Packaged one per kit.



FOR SHAFT END OF 48 FRAME MOTORS

SHLD6301

Ventilated with flat face
1/2" Sleeve Bearing.



SHLD6312

Non-Ventilated with flat face
5/8" Sleeve Bearing.



FOR SHAFT END OF 48 FRAME MOTORS (CONTINUED)

SHLD6303

Ventilated with double oiling hub
1/2" Sleeve Bearing.



SHLD6311

Ventilated with flat face
5/8" Sleeve Bearing.



SHLD6302

Non-Ventilated with double oiling hub
1/2" Sleeve Bearing.



SHLD6304

Non-Ventilated with flat face
1/2" Sleeve Bearing.



KIT410

End Shield caps for 48 frame.
10 per kit (5 open, 5 closed).





MOUNTING KITS

KIT200

Holes for 4.4" and 5.6" diameter motors.
One kit will adapt both ends of motor for base mounting.



KIT199

Motor length adapter kit.
Provides means to base mount Fasco 5" diameter motors.
Two kits needed to adapt both ends of motor for base mounting.



KIT380

Rheem mounting adapter plate.
Packaged one per kit.



KIT214

Special end plate for 3.3" diameter D401 motor.
For mounting to Comfort Air units.
Packaged one per kit.




KIT218

Aluminum stand-off bracket for motor-blower mounting.
Matches 3.3" mounting pattern.
Kit 214 required to mount to motor.
Packaged one per kit.



ADAPTER PLATES



KIT207

Provides rectangular mounting stud pattern on 5.0" or 5.6" diameter Fasco motors to match Fedders stud motors.
Similar to Emerson and RMR rectangular mounting stud patterns.
Packaged one per kit.

KIT205


Franklin Redmond 4 1/8" diameter mounting adapter plate.
Packaged one per kit.



ADAPTER KITS

KIT538

Mounting adapter enables 5" motors to replace 5 3/8" (RMR) motors.
Three adapters included in kit.
Adapters increase the mounting diameter by 3/8" for belly band mounting.



NOTE: Thermally protected • UL recognized • CSA or ULc certified
Rotation is determined by looking at shaft end. Shaft length is measured from motor face.



MOUNTING ADAPTER KITS & PARTS

RHEEM MOUNTING CABLES

PART NO.	LENGTH	MOTOR H.P.
KIT325	3-1/4	1/6
KIT350	3-1/2	1/4
KIT378	3-1/8	1/3

Special mounting cables for Rheem. Four per pkg.



H33

Special mounting kit for 3.3" diameter to replace motors in Nu-tone units.

Includes four nuts and two hex hub brackets.

Use Kit 187 mounting rings.



KIT414

Adjustable casebolt mounting kit.

Four bolt adapters per kit.



COLEMAN "LORD" MOUNT

MNT1518

Stud: 1/4 x 8-32
Hole: 1/4 x 8-32
Bushing: 1/2 x 1/2
Shipped individually.



KIT208


Studs: 3/8" x 8-32 x 3/8"
Bushing: 1/2" x 1/2"
Four per kit.



MOUNTING GROMMETS

GROM6008

For 3/4" slot.
Shipped individually.



Includes a Steel Sleeve

GROM6000

For 1/2" slot.
Shipped individually.



RUBBER MOUNTING RINGS

FOR 5.6", 5.0" AND 4.4" DIAMETER MOTORS

KIT184

Henrite 2.50

Packaged two per kit.



KIT183

Henrite 2.25 O.D.

Packaged two per kit.



KIT186

All Rubber 2.50 O.D.

Packaged two per kit.



FOR 3.3" DIAMETER MOTORS

KIT180

Henrite 1.80 O.D.

Packaged two per kit.



KIT187

Rubber mounting rings; use with H33 in Nutone and Broan applications.
Packaged two per kit.



Henrite are rubber mounting rings with steel band, used with cradle bases and knife edge motor supports.

All Rubber rings are used with direct drive blower motors and "Clamp" type supports.



CAPACITORS



PART NO.	RATING		STYLE
6100-6028*	2 mfd	370V	Oval
6100-9020*	3 mfd	370V	Oval
6100-9006*	4 mfd	370V	Oval
6100-6119*	5 mfd	370V	Oval
6100-9085*	5 mfd	440V	Oval
6100-9010*	6 mfd	370V	Oval
6100-6120*	7.5 mfd	370V	Oval
6100-9088*	7.5 mfd	440V	Oval
6100-6121*	10 mfd	370V	Oval
6100-6002*	10 mfd	440V	Oval
6100-6030*	12.5 mfd	370V	Oval
6100-9037	15 mfd	370V	Oval
6100-6031	17.5 mfd	370V	Oval
6100-9053	20 mfd	370V	Oval
6100-6032	25 mfd	370V	Oval
6100-6033	30 mfd	370V	Oval
6100-6034	35 mfd	370V	Oval
6100-6035	40 mfd	370V	Oval
6100-6036	45 mfd	370V	Oval
6100-6037	50 mfd	370V	Oval
6100-6038	60 mfd	370V	Oval
6100-6019	8 mfd	370V	Round
6100-6020	10 mfd	370V	Round
6100-6021	12 mfd	370V	Round
6100-6022	15 mfd	370V	Round
6100-6023	20 mfd	370V	Round
6100-6024	25 mfd	370V	Round
6100-6025	30 mfd	370V	Round
6100-6026	35 mfd	370V	Round
6100-6027	40 mfd	370V	Round

* Will fit Kit 6001

MISCELLANEOUS KITS

CAPACITOR MOUNTING KIT

KIT6001

Rubber boot and bracket.

RUBBERBOOT

Rubber boot sold separately.



STAKED TIE RODS QTY. 4

KIT220

8" long 8-32 NC for Fasco 5.6" diameter motors.

Includes one staked nut and one regular nut.

KIT221

8" long 10-32 NC for Fasco 4.4" diameter motors.



KIT832

8-32 Nuts, 32 pieces



KIT1032

10-32 Nuts, 32 pieces



Thermally protected • UL recognized • GSA or ULc certified
NOTE: Rotation is determined by looking at shaft end. Shaft length is measured from motor face.




NEOPRENE GASKET

GASKET0167

Includes one gasket and four grommets.

- 3.3" diameter motors
- 2.84" Bolt Circle diameter



WATER SLINGER

SLINGR6002

1/2" I.D. x 2" O.D.
Shipped individually.



SHAFT BUSHINGS QTY. 4

KIT240

1/4" ID x 5/16" OD

KIT242

3/8" ID x 1/2" OD

KIT244

5/16" ID x 3/8" OD

KIT246

1/2" ID x 5/8" OD



RAIN SHIELDS

KIT170

For 1/2" shaft diameter motors.

RAIN6000

For 5/8" shaft diameter motors.



KIT465

Anderol 465 synthetic lubricating oil (3 oz.).
Packaged one per carton.



COOLING FAN KIT FOR DRAFT BOOSTER MOTORS

FK100

C.W. rotation
1 3/4" diameter
1/4" Hub I.D.

FK101

C.C.W. rotation
1 3/4" diameter
1/4" Hub I.D.
Shipped one fan per kit.



Rotation is facing
side opposite hub